

Product Details and Certifications

Product: 140U-K6D3-D40

Description: Molded Case Circuit Breaker, 400A, K-Frame, T/M - Fixed Thermal / Adjustable Magnetic, Rated Current 400A



Representative Photo Only (actual product may vary based on configuration selections)

System Data

Supply Voltage	600V 60Hz
Maximum Available Fault Current (at the Breaker)	5 kA

Circuit Breaker Data

Is a Current Limiting Circuit Breaker Required?	No, a Current Limiting Circuit Breaker is Not Required
Pole Configuration	3 Poles
Interrupt Rating [kA]	35 kA @ 600V, 65 kA @ 480V
Protection	T/M - Fixed Thermal / Adjustable Magnetic
Rated Current (A)	400
Rating / Frame Size	400A, K-Frame

Manufacturing

Assembly	Factory Assembled
----------	-------------------

Terminal Lug Data

Important Information!	Terminal Lugs are not Factory Installed. See below to order.
------------------------	--

Internal Control Modules, Factory Installed

Shunt Trip (SNT) and Undervoltage Release (UVT), Left Side Mounting	None
Voltage	None
Auxiliaries (AX), Alarm (AL), Auxiliary/Alarm Combination (AX/AL), Right Side Mounting	None

Mounting Data

Busbar Mounting (Only for Use with 141A Mounting System)	None
--	------

Certifications and Approvals

UL	489
CSA	22.2, No. 5
For UL Certifications Directory:	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm