

Product: 140U-K6G3-D40
Description: 140U Molded Case Circuit Breakers



Representati
 Photo Only (actual product ma
 vary based on configuration
 selections)

System Data

Supply Voltage 480V 60Hz

Circuit Breaker Data

Current Limitation Required? No
 Pole Configuration 3 Poles
 Rated Current (A) 400
 Protection Electronic LSG - Long & Short Time, Ground Fault
 Frame Size K-Frame (up to 400A)
 Interrupt Rating [kA] 65 kA

Manufacturing

Assembly Factory Assembled

Internal Control Modules, Factory Installed

Shunt Trip (SNT) and Undervoltage Release (UVT), Left Side Mounting None
 Voltage None
 Auxiliaries (AX), Alarm (AL), Auxiliary/Alarm Combination (AX/AL), Right Side Mounting None

Mounting Data

Busbar Mounting (Only for Use with 141A Mounting System) None

CERTIFICATIONS AND APPROVALS

UL 489
 CSA 22.2, No. 5
 For UL Certifications Directory: <http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>