



## Equipment List

Item	Product	Qty	Notes	Typical Delivery	DS	PGC	List Price	Sell Mult	Net (Ea)	Ext Net	Wt (lbs)	UPC	UNSPSC	KMAT	VAT	Cost Mult	Cost (Ea)	Ext Cost	Margin	Margin (Ea)	Ext Margin
1	<b>1485R-P2M5-R5</b> <i>DeviceNet, Trunk End: Mini, Straight Male, Device End: Micro, Straight Female, Thin Media, Yellow CPE,</i>	1		Preferred Availability	E9	648	\$58.48	1	\$58.48	\$58.48	0.15309	10662468421352	26121609		0	1	\$58.48	\$58.48	0	\$0.00	\$0.00
<b>GRAND TOTAL:</b>																					
Sell: \$58.48																					
Cost: \$58.48																					
Margin: \$0.00																					

## Product Details and Certifications

**Product:** 1485R-P2M5-R5

**Description:** 1485 DeviceNet Patchcords and Cordsets

### CABLE DATA

Cable Type	Thin Media, Yellow CPE
Coupling Nut Material	Standard - Epoxy Coated Zinc
Cable Details	Standard Passive Cable
Standard or Build-to-Order Cable Length	2 meters (6.56 feet)
First End Connector Style	Mini, Straight Male
Number of Pins	Standard 5-pin

### DEVICE END DATA

Second End Termination Style	Micro, Straight Female
Second End Conductors	Standard 5-pin