

# Product Details and Certifications

**Cross Reference RA Part Number: 1492-CJL8-32 A**

 **Product: 1492-CJL8-32**

Description: Plug-In Center Jumper, 8 mm Center to Center,  
32 Poles, Gray



Representative Photo Only (actual product may vary based on configuration sections)

## ***ACCESSORY SELECTION***

---

Bulletin Number	1492 IEC Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

## ***SELECTION***

---

Screw Type Center Jumpers

# Spring-Clamp Connection Terminal Blocks

## Standard Feed-Through Blocks

	1492-L6				1492-L6T				1492-L10			
Dimensions are not intended to be used for manufacturing purposes. <b>Note:</b> Height dimension is measured from top of rail to top of terminal block.												
	Feed-through terminal block				Feed-through terminal block with 2 connection points on one side				Feed-through terminal block			
<b>Specifications</b>												
Certifications		CSA	IEC	ATEX		CSA	IEC	ATEX		CSA	IEC	ATEX
Voltage Rating	600V AC/DC			800V AC/DC	550V AC/DC	600V AC/DC			800V AC/DC	550V AC/DC	600V AC/DC	
Maximum Current	50 A		41 A	36 A	50 A		41 A	36 A	60 A	55 A	57 A	50 A
Wire Range (Rated Cross Section)	#22...8 AWG	#20...8 AWG	6 mm <sup>2</sup>	6 mm <sup>2</sup> (20...8 AWG)	#22...8 AWG	#20...8 AWG	6 mm <sup>2</sup>	6 mm <sup>2</sup> (#20...10 AWG)	#16...6 AWG	10 mm <sup>2</sup>	10 mm <sup>2</sup> (16...8 AWG)	10 mm <sup>2</sup> (16...8 AWG)
Wire Strip Length	0.51 in. (13 mm)				0.51 in. (13 mm)				0.70 in. (18 mm)			
Density	37 pcs/ft (123 pcs/m)				37 pcs/ft(123 pcs/m)				30 pcs/ft (99 pcs/m)			
Housing Temperature Range	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)			
Short-Circuit Current Rating	See page 12-78											
<b>Terminal Blocks</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>
Color	Grey	<b>1492-L6</b>	50		<b>1492-L6T</b>	50		<b>1492-L10</b>	25			
	Red	<b>1492-L6-RE</b>	50		<b>1492-L6T-RE</b>	50		1492-L10-RE	25			
	Blue	1492-L6-B	50		<b>1492-L6T-B</b>	50		1492-L10-B	25			
	Black	<b>1492-L6-BL</b>	50		<b>1492-L6T-BL</b>	50		<b>1492-L10-BL</b>	25			
	Green	<b>1492-L6-G</b>	50		<b>1492-L6T-G</b>	50		1492-L10-G	25			
	Yellow	1492-L6-Y	50		1492-L6T-Y	50		1492-L10-Y	25			
	Orange	1492-L6-OR	50		1492-L6T-OR	50		1492-L10-OR	25			
	Brown	1492-L6-BR	50		1492-L6T-BR	50		1492-L10-BR	25			
	White	<b>1492-L6-W</b>	50		1492-L6T-W	50		1492-L10-W	25			
<b>Accessories</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>
Mounting Rails												
1 m Symmetrical DIN (Steel)		<b>199-DR1</b>	10		<b>199-DR1</b>	10		<b>199-DR1</b>	10			
1 m Symmetrical DIN (Aluminum)		<b>1492-DR5</b>	10		<b>1492-DR5</b>	10		<b>1492-DR5</b>	10			
1 m Hi-Rise Sym. DIN (Aluminum)		<b>1492-DR6</b>	2		<b>1492-DR6</b>	2		<b>1492-DR6</b>	2			
1 m Angled Hi-Rise Sym. DIN (Steel)		<b>1492-DR7</b>	2		<b>1492-DR7</b>	2		<b>1492-DR7</b>	2			
End Barriers	Grey	<b>1492-EBL6</b>	50		<b>1492-EBL6T</b>	50		<b>1492-EBL10</b>	20			
	Blue	1492-EBL6-B	50		1492-EBL6T-B	50		1492-EBL10-B	20			
	Yellow	<b>1492-EBL6-Y</b>	50		<b>1492-EBL6T-Y</b>	50		<b>1492-EBL10-Y</b>	20			
End Anchors and Retainers												
Screwless End Retainer		<b>1492-ERL35</b>	20		<b>1492-ERL35</b>	20		<b>1492-ERL35</b>	20			
DIN Rail — Normal Duty		<b>1492-EAJ35</b>	100		<b>1492-EAJ35</b>	100		<b>1492-EAJ35</b>	100			
DIN Rail — Heavy Duty		<b>1492-EAHJ35</b>	50		<b>1492-EAHJ35</b>	50		<b>1492-EAHJ35</b>	50			
<b>Jumpers</b>												
Plug-in Center Jumper — 32-Pole		<b>1492-CJL8-32</b>	10		<b>1492-CJL8-32</b>	10		—	—			
Plug-in Center Jumper — 4-Pole		<b>1492-CJL8-4</b>	60		<b>1492-CJL8-4</b>	60		—	—			
Plug-in Center Jumper — 3-Pole		<b>1492-CJL8-3</b>	60		<b>1492-CJL8-3</b>	60		—	—			
Plug-in Center Jumper — 2-Pole		<b>1492-CJL8-2</b>	60		<b>1492-CJL8-2</b>	60		<b>1492-CJL10-2</b>	25			
Other Accessories												
Test Plug		—	—		—	—		<b>1492-TP23</b>	20			
Test Plug (Stackable)		1492-TPL8	25		1492-TPL8	25		—	—			
Electrical Warning Plate		1492-EWPL8	20		1492-EWPL8	20		1492-EWPL10	20			
Marking Systems												
Snap-In Marker Cards*		<b>1492-M6X12</b> (120/card)	5		<b>1492-M6X12</b> (120/card)	5		<b>1492-M6X12</b> (120/card)	5			
Snap-In Marker Cards		<b>1492-MR8X12</b> (84/card)	5		<b>1492-M8X5</b> (160/card)	5		<b>1492-M8X5</b> (160/card)	5			
Hinged Marker Cards		<b>1492-MH6X12</b> (80/card)	5		<b>1492-MH6X12</b> (80/card)	5		<b>1492-MH5X15</b> (96/card)	5			

\* May only be mounted in terminal block corner marking positions.