

# Product Details and Certifications

**Cross Reference RA Part Number: 1492-CJLJ6-10 A**



**Product: 1492-CJLJ6-10**

Description: Plug-In Center Jumper, 6 mm Center to Center,  
10 Poles, Gray



Representative Photo Only (actual product may vary based on configuration sections)

## ***ACCESSORY SELECTION***

---

Bulletin Number	1492 IEC Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

## ***SELECTION***

---

Screw Type Center Jumpers

# Screw Connection Terminal Blocks

## Multi-Circuit Feed-Through Blocks

	1492-JD3				1492-JD4				1492-JT3M		
Dimensions are not intended to be used for manufacturing purposes. <b>Note:</b> Height dimension is measured from top of rail to top of terminal block.											
	<b>Specifications</b> <i>Two-level, two-circuit feed-through terminal block</i>				<i>Two-level, two-circuit feed-through terminal block</i>				<i>Three-level, three-circuit terminal block with ground point</i>		
Certifications		CSA	IEC	ATEX		CSA	IEC	ATEX		CSA	IEC
Voltage Rating	600V AC/DC	300V AC/DC	400V AC/DC	275V AC/DC	600V AC/DC	300V AC/DC	800V AC/DC	550V AC/DC	300V AC/DC		400V AC/DC
Maximum Current	20 A	10 A	24 A	21 A	35 A	30 A	32 A	28 A	10 A		24 A
Wire Range (Rated Cross Section)	#22...12 AWG	26...12 AWG	2.5 mm <sup>2</sup>	2.5 mm <sup>2</sup> (20...14 AWG)	#26...10 AWG	0.5...4 mm <sup>2</sup>		4 mm <sup>2</sup> (20...12 AWG)	#22...12 AWG	#26...10 AWG	0.5...2.5 mm <sup>2</sup>
Wire Strip Length	0.39 in. (10 mm)				0.315 in. (8 mm)				0.28 in. (7 mm)		
Recommended Tightening Torque	4.5...7.1 lb•in (0.5...0.8 N•m)				4.5 lb•in (0.5 N•m)				4.4 lb•in (0.5 N•m)		
Density	59 pcs/ft (196 pcs/m)				49 pcs/ft (163 pcs/m)				49 pcs/ft (163 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)		
Short-Circuit Current Rating	See page 12-42										
<b>Terminal Blocks</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		
Color:	Grey	<b>1492-JD3</b>	100		<b>1492-JD4</b>	100		<b>1492-JT3M</b>	50		
	Red	<b>1492-JD3-RE</b>	100		<b>1492-JD4-RE</b>	100		—	—		
	Blue	<b>1492-JD3-B</b>	100		<b>1492-JD4-B</b>	100		—	—		
	Black	<b>1492-JD3-BL</b>	100		1492-JD4-BL	100		—	—		
	Green	<b>1492-JD3-G</b>	100		1492-JD4-G	100		—	—		
	Yellow	<b>1492-JD3-Y</b>	100		1492-JD4-Y	100		—	—		
	Orange	<b>1492-JD3-OR</b>	100		<b>1492-JD4-OR</b>	100		—	—		
	Brown	<b>1492-JD3-BR</b>	100		1492-JD4-BR	100		—	—		
	White	<b>1492-JD3-W</b>	100		<b>1492-JD4-W</b>	100		—	—		
<b>Accessories</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		
Mounting Rails:											
1 m Symmetrical DIN (Steel)		<b>199-DR1</b>	10		<b>199-DR1</b>	10		<b>199-DR1</b>	10		
1 m Symmetrical DIN (Aluminum)		<b>1492-DR5</b>	10		<b>1492-DR5</b>	10		<b>1492-DR5</b>	10		
1 m Hi-Rise Sym. DIN (Aluminum)		<b>1492-DR6</b>	2		<b>1492-DR6</b>	2		<b>1492-DR6</b>	2		
1 m Angled Hi-Rise Sym. DIN (Steel)		<b>1492-DR7</b>	2		<b>1492-DR7</b>	2		<b>1492-DR7</b>	2		
End Barrier	Grey	<b>1492-EBJD3</b>	20		<b>1492-EBJD4</b>	20		<b>1492-EBJ3TM</b>	20		
	Blue	<b>1492-EBJD3-B</b>	20		<b>1492-EBJD4-B</b>	20		—	—		
	Yellow	<b>1492-EBJD3-Y</b>	20		—	—		—	—		
End Anchor and Retainers:											
Screwless End Retainer		<b>1492-ERL35</b>	20		—	—		—	—		
DIN Rail — Normal Duty		<b>1492-EAJ35</b>	100		—	—		—	—		
DIN Rail — Heavy Duty		<b>1492-EAHJ35</b>	50		<b>1492-EAHJ35</b>	50		<b>1492-EAHJ35</b>	50		
Jumpers:											
Center Jumper — 41-pole		—	—	‡	<b>1492-CJLJ6-41</b>	10		—	—		
<b>Center Jumper — 10-pole</b>	⊛	<b>1492-CJJ5-10</b>	20	‡	<b>1492-CJLJ6-10</b>	10		—	—		
Center Jumper — 4-pole	⊛	<b>1492-CJJ5-4</b>	50	‡	<b>1492-CJLJ6-4</b>	60		—	—		
Center Jumper — 3-pole	⊛	<b>1492-CJJ5-3</b>	50	‡	<b>1492-CJLJ6-3</b>	60		—	—		
Center Jumper — 2-pole	⊛	<b>1492-CJJ5-2</b>	50	‡	<b>1492-CJLJ6-2</b>	60		—	—		
Insulated Side Jumper — 50-Pole		—	—		—	—		<b>1492-SJ6A-50</b>	5		
Insulated Side Jumper — 24-Pole		<b>1492-SJ5A-24</b>	50		—	—		—	—		
Insulated Side Jumper — 10-Pole		<b>1492-SJ5A-10</b>	50		—	—		—	—		
Screw Type Jumper Notching Tool		<b>1492-T1</b>	1		—	—		—	—		
Other Accessories:											
Partition Plate		<b>1492-PPJD3</b>	20		<b>1492-PPJD3</b>	20		<b>1492-PPJD3</b>	20		
Test Plug Socket		<b>1492-TPS23</b>	20		—	—		—	—		
Test Plug		<b>1492-TP23</b>	20		—	—		—	—		
Snap-in marker cards		<b>1492-M5X5</b> (200/card)	5		<b>1492-M6X5</b> (200/card)	5		<b>1492-M6X5</b> (200/card)	5		
Snap-in marker cards		<b>1492-M5X8</b> (144/card)	5		<b>1492-MR6X8</b> (120/card)	5		<b>1492-MR6X8</b> (120/card)	5		

⊛ Screw Center Jumpers, ‡ Plug-in Center Jumpers