

Product Details and Certifications

Cross Reference RA Part Number: 1492-CJLJ6-41 A



Product: 1492-CJLJ6-41

Description: Plug-In Center Jumper, 6 mm Center to Center,
41 Poles, Gray



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number	1492 IEC Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

SELECTION

Screw Type Center Jumpers

Screw Connection Terminal Blocks

Multi-Circuit Feed-Through Blocks

	1492-JD3				1492-JD4				1492-JT3M		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.											
	Specifications <i>Two-level, two-circuit feed-through terminal block</i>				<i>Two-level, two-circuit feed-through terminal block</i>				<i>Three-level, three-circuit terminal block with ground point</i>		
Certifications		CSA	IEC	ATEX		CSA	IEC	ATEX		CSA	IEC
Voltage Rating	600V AC/DC	300V AC/DC	400V AC/DC	275V AC/DC	600V AC/DC	300V AC/DC	800V AC/DC	550V AC/DC	300V AC/DC		400V AC/DC
Maximum Current	20 A	10 A	24 A	21 A	35 A	30 A	32 A	28 A	10 A		24 A
Wire Range (Rated Cross Section)	#22...12 AWG	26...12 AWG	2.5 mm ²	2.5 mm ² (20...14 AWG)	#26...10 AWG	0.5...4 mm ²		4 mm ² (20...12 AWG)	#22...12 AWG	#26...10 AWG	0.5...2.5 mm ²
Wire Strip Length	0.39 in. (10 mm)				0.315 in. (8 mm)				0.28 in. (7 mm)		
Recommended Tightening Torque	4.5...7.1 lb•in (0.5...0.8 N•m)				4.5 lb•in (0.5 N•m)				4.4 lb•in (0.5 N•m)		
Density	59 pcs/ft (196 pcs/m)				49 pcs/ft (163 pcs/m)				49 pcs/ft (163 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)		
Short-Circuit Current Rating	See page 12-42										
Terminal Blocks		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		
Color:	Grey	1492-JD3	100		1492-JD4	100		1492-JT3M	50		
	Red	1492-JD3-RE	100		1492-JD4-RE	100		—	—		
	Blue	1492-JD3-B	100		1492-JD4-B	100		—	—		
	Black	1492-JD3-BL	100		1492-JD4-BL	100		—	—		
	Green	1492-JD3-G	100		1492-JD4-G	100		—	—		
	Yellow	1492-JD3-Y	100		1492-JD4-Y	100		—	—		
	Orange	1492-JD3-OR	100		1492-JD4-OR	100		—	—		
	Brown	1492-JD3-BR	100		1492-JD4-BR	100		—	—		
	White	1492-JD3-W	100		1492-JD4-W	100		—	—		
Accessories		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		
Mounting Rails:											
1 m Symmetrical DIN (Steel)		199-DR1	10		199-DR1	10		199-DR1	10		
1 m Symmetrical DIN (Aluminum)		1492-DR5	10		1492-DR5	10		1492-DR5	10		
1 m Hi-Rise Sym. DIN (Aluminum)		1492-DR6	2		1492-DR6	2		1492-DR6	2		
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7	2		1492-DR7	2		1492-DR7	2		
End Barrier	Grey	1492-EBJD3	20		1492-EBJD4	20		1492-EBJ3TM	20		
	Blue	1492-EBJD3-B	20		1492-EBJD4-B	20		—	—		
	Yellow	1492-EBJD3-Y	20		—	—		—	—		
End Anchor and Retainers:											
Screwless End Retainer		1492-ERL35	20		—	—		—	—		
DIN Rail — Normal Duty		1492-EAJ35	100		—	—		—	—		
DIN Rail — Heavy Duty		1492-EAHJ35	50		1492-EAHJ35	50		1492-EAHJ35	50		
Jumpers:											
Center Jumper — 41-pole		—	—		1492-CJLJ6-41	—		—	—		
Center Jumper — 10-pole		1492-CJJ5-10	20		1492-CJLJ6-10	20		—	—		
Center Jumper — 4-pole		1492-CJJ5-4	50		1492-CJLJ6-4	60		—	—		
Center Jumper — 3-pole		1492-CJJ5-3	50		1492-CJLJ6-3	60		—	—		
Center Jumper — 2-pole		1492-CJJ5-2	50		1492-CJLJ6-2	60		—	—		
Insulated Side Jumper — 50-Pole		—	—		—	—		1492-SJ6A-50	5		
Insulated Side Jumper — 24-Pole		1492-SJ5A-24	50		—	—		—	—		
Insulated Side Jumper — 10-Pole		1492-SJ5A-10	50		—	—		—	—		
Screw Type Jumper Notching Tool		1492-T1	1		—	—		—	—		
Other Accessories:											
Partition Plate		1492-PPJD3	20		1492-PPJD3	20		1492-PPJD3	20		
Test Plug Socket		1492-TPS23	20		—	—		—	—		
Test Plug		1492-TP23	20		—	—		—	—		
Snap-in marker cards		1492-M5X5 (200/card)	5		1492-M6X5 (200/card)	5		1492-M6X5 (200/card)	5		
Snap-in marker cards		1492-M5X8 (144/card)	5		1492-MR6X8 (120/card)	5		1492-MR6X8 (120/card)	5		

* Screw Center Jumpers, ‡ Plug-in Center Jumpers

Plug-in Center Jumpers