

# Product Details and Certifications

**Cross Reference RA Part Number: 1492-EBL2T A**

 **Product: 1492-EBL2T**

Description: 1492 Terminal Block, End Barrier, Gray ( Standard), Qty.50



Representative Photo Only (actual product may vary based on configuration sections)

## ***ACCESSORY SELECTION***

---

|                     |                                 |
|---------------------|---------------------------------|
| Bulletin Number     | 1492 Terminal Block Accessories |
| Accessory Selection | Individual Accessory Selection  |

## ***SELECTION***

---

1492 Accessory

# Spring-Clamp Connection Terminal Blocks

## Standard Feed-Through Blocks

|  | 1492-L2                            |                              |                     |                     | 1492-L2T  |                              |                     |                     | 1492-L2Q   |                              |                     |                     |
|--|------------------------------------|------------------------------|---------------------|---------------------|---|------------------------------|---------------------|---------------------|--|------------------------------|---------------------|---------------------|
| Dimensions are not intended to be used for manufacturing purposes.<br><b>Note:</b> Height dimension is measured from top of rail to top of terminal block. |                                    |                              |                     |                     |   |                              |                     |                     |  |                              |                     |                     |
| <b>Specifications</b>  | <i>Feed-through terminal block</i> |                              |                     |                     | <i>Feed-through terminal block with 2 connection points on one side</i> |                              |                     |                     | <i>Feed-through terminal block with 2 connection points per side</i> |                              |                     |                     |
| <b>Certifications</b>  |                                    | <b>CSA</b>                   | <b>IEC</b>          | <b>ATEX</b>         |   | <b>CSA</b>                   | <b>IEC</b>          | <b>ATEX</b>         |  | <b>CSA</b>                   | <b>IEC</b>          | <b>ATEX</b>         |
| <b>Voltage Rating</b>  | 300V AC/DC                         |                              | 500V AC/DC          | 550V AC/DC          | 300V AC/DC  |                              | 500V AC/DC          | 550V AC/DC          | 300V AC/DC   |                              | 500V AC/DC          | 550V AC/DC          |
| <b>Maximum Current</b>   | 15 A                               | 20 A                         | 17.5 A              | 15 A                | 15 A  | 20 A                         | 17.5 A              | 15 A                | 15 A   | 20 A                         | 17.5 A              | 15 A                |
| <b>Wire Range (Rated Cross Section)</b>  | #26...14 AWG                       |                              | 1.5 mm <sup>2</sup> | 1.5 mm <sup>2</sup> | #26...14 AWG  |                              | 1.5 mm <sup>2</sup> | 1.5 mm <sup>2</sup> | #26...14 AWG   |                              | 1.5 mm <sup>2</sup> | 1.5 mm <sup>2</sup> |
| <b>Wire Strip Length</b>   | 0.39 in. (10 mm)                   |                              |                     |                     | 0.39 in. (10 mm)  |                              |                     |                     | 0.39 in. (10 mm)   |                              |                     |                     |
| <b>Density</b>   | 87 pcs/ft (285 pcs/m)              |                              |                     |                     | 87 pcs/ft (285 pcs/m)   |                              |                     |                     | 87 pcs/ft (285 pcs/m)  |                              |                     |                     |
| <b>Housing Temperature Range</b>   | -58...+248 °F (-50...+120 °C)      |                              |                     |                     | -58...+248 °F (-50...+120 °C)   |                              |                     |                     | -58...+248 °F (-50...+120 °C)  |                              |                     |                     |
| <b>Terminal Blocks</b>   |                                    | <b>Cat. No.</b>              |                     | <b>Pkg Qty.</b>     |   | <b>Cat. No.</b>              |                     | <b>Pkg Qty.</b>     |  | <b>Cat. No.</b>              |                     | <b>Pkg Qty.</b>     |
| <b>Color</b>   | Grey                               | <b>1492-L2</b>               |                     | 50                  |   | <b>1492-L2T</b>              |                     | 50                  |  | <b>1492-L2Q</b>              |                     | 50                  |
|  | Red                                | <b>1492-L2-RE</b>            |                     | 50                  |   | <b>1492-L2T-RE</b>           |                     | 50                  |  | <b>1492-L2Q-RE</b>           |                     | 50                  |
|  | Blue                               | <b>1492-L2-B</b>             |                     | 50                  |   | <b>1492-L2T-B</b>            |                     | 50                  |  | <b>1492-L2Q-B</b>            |                     | 50                  |
|  | Black                              | <b>1492-L2-BL</b>            |                     | 50                  |   | <b>1492-L2T-BL</b>           |                     | 50                  |  | <b>1492-L2Q-BL</b>           |                     | 50                  |
|  | Green                              | <b>1492-L2-G</b>             |                     | 50                  |   | <b>1492-L2T-G</b>            |                     | 50                  |  | <b>1492-L2Q-G</b>            |                     | 50                  |
|  | Yellow                             | <b>1492-L2-Y</b>             |                     | 50                  |   | <b>1492-L2T-Y</b>            |                     | 50                  |  | <b>1492-L2Q-Y</b>            |                     | 50                  |
|  | Orange                             | <b>1492-L2-OR</b>            |                     | 50                  |   | <b>1492-L2T-OR</b>           |                     | 50                  |  | <b>1492-L2Q-OR</b>           |                     | 50                  |
|  | Brown                              | <b>1492-L2-BR</b>            |                     | 50                  |   | <b>1492-L2T-BR</b>           |                     | 50                  |  | <b>1492-L2Q-BR</b>           |                     | 50                  |
|  | White                              | <b>1492-L2-W</b>             |                     | 50                  |   | <b>1492-L2T-W</b>            |                     | 50                  |  | <b>1492-L2Q-W</b>            |                     | 50                  |
| <b>Accessories</b>   |                                    | <b>Cat. No.</b>              |                     | <b>Pkg Qty.</b>     |   | <b>Cat. No.</b>              |                     | <b>Pkg Qty.</b>     |  | <b>Cat. No.</b>              |                     | <b>Pkg Qty.</b>     |
| <b>Mounting Rails</b>  |                                    |                              |                     |                     |   |                              |                     |                     |  |                              |                     |                     |
| 1 m Symmetrical DIN (Steel)  |                                    | <b>199-DR1</b>               |                     | 10                  |   | <b>199-DR1</b>               |                     | 10                  |  | <b>199-DR1</b>               |                     | 10                  |
| 1 m Symmetrical DIN (Aluminum)   |                                    | <b>1492-DR5</b>              |                     | 10                  |   | <b>1492-DR5</b>              |                     | 10                  |  | <b>1492-DR5</b>              |                     | 10                  |
| 1 m Hi-Rise Sym. DIN (Aluminum)  |                                    | <b>1492-DR6</b>              |                     | 2                   |   | <b>1492-DR6</b>              |                     | 2                   |  | <b>1492-DR6</b>              |                     | 2                   |
| 1 m Angled Hi-Rise Sym. DIN (Steel)  |                                    | <b>1492-DR7</b>              |                     | 2                   |   | <b>1492-DR7</b>              |                     | 2                   |  | <b>1492-DR7</b>              |                     | 2                   |
| <b>End Barriers</b>  | Grey                               | <b>1492-EBL2</b>             |                     | 50                  |   | <b>1492-EBL2T</b>            |                     | 50                  |  | <b>1492-EBL2Q</b>            |                     | 50                  |
|  | Blue                               | <b>1492-EBL2-B</b>           |                     | 50                  |   | <b>1492-EBL2T-B</b>          |                     | 50                  |  | <b>1492-EBL2Q-B</b>          |                     | 50                  |
|  | Yellow                             | <b>1492-EBL2-Y</b>           |                     | 50                  |   | <b>1492-EBL2T-Y</b>          |                     | 50                  |  | <b>1492-EBL2Q-Y</b>          |                     | 50                  |
| <b>End Anchors and Retainers</b>   |                                    |                              |                     |                     |   |                              |                     |                     |  |                              |                     |                     |
| Screwless End Retainer   |                                    | <b>1492-ERL35</b>            |                     | 20                  |   | <b>1492-ERL35</b>            |                     | 20                  |  | <b>1492-ERL35</b>            |                     | 20                  |
| DIN Rail — Normal Duty   |                                    | <b>1492-EAJ35</b>            |                     | 100                 |   | <b>1492-EAJ35</b>            |                     | 100                 |  | <b>1492-EAJ35</b>            |                     | 100                 |
| DIN Rail — Heavy Duty  |                                    | <b>1492-EAHJ35</b>           |                     | 50                  |   | <b>1492-EAHJ35</b>           |                     | 50                  |  | <b>1492-EAHJ35</b>           |                     | 50                  |
| <b>Jumpers</b>   |                                    |                              |                     |                     |   |                              |                     |                     |  |                              |                     |                     |
| Plug-in Center Jumper — 10-Pole  |                                    | <b>1492-CJL4-10</b>          |                     | 20                  |   | <b>1492-CJL4-10</b>          |                     | 20                  |  | <b>1492-CJL4-10</b>          |                     | 20                  |
| Plug-in Center Jumper — 5-Pole   |                                    | <b>1492-CJL4-5</b>           |                     | 60                  |   | <b>1492-CJL4-5</b>           |                     | 60                  |  | <b>1492-CJL4-5</b>           |                     | 60                  |
| Plug-in Center Jumper — 4-Pole   |                                    | <b>1492-CJL4-4</b>           |                     | 60                  |   | <b>1492-CJL4-4</b>           |                     | 60                  |  | <b>1492-CJL4-4</b>           |                     | 60                  |
| Plug-in Center Jumper — 3-Pole   |                                    | <b>1492-CJL4-3</b>           |                     | 60                  |   | <b>1492-CJL4-3</b>           |                     | 60                  |  | <b>1492-CJL4-3</b>           |                     | 60                  |
| Plug-in Center Jumper — 2-Pole   |                                    | <b>1492-CJL4-2</b>           |                     | 60                  |   | <b>1492-CJL4-2</b>           |                     | 60                  |  | <b>1492-CJL4-2</b>           |                     | 60                  |
| <b>Other Accessories</b>   |                                    |                              |                     |                     |   |                              |                     |                     |  |                              |                     |                     |
| Reducing Sleeves #28...#24 AWG (0.13...0.2 mm <sup>2</sup> ) White   |                                    | <b>1492-PSL2-2</b>           |                     | 100                 |   | <b>1492-PSL2-2</b>           |                     | 100                 |  | <b>1492-PSL2-2</b>           |                     | 100                 |
| Reducing Sleeves #22...#20 AWG (0.25...0.5 mm <sup>2</sup> ) Grey  |                                    | <b>1492-PSL2-5</b>           |                     | 100                 |   | <b>1492-PSL2-5</b>           |                     | 100                 |  | <b>1492-PSL2-5</b>           |                     | 100                 |
| Test Plug (Stackable)  |                                    | <b>1492-TPL4</b>             |                     | 25                  |   | <b>1492-TPL4</b>             |                     | 25                  |  | <b>1492-TPL4</b>             |                     | 25                  |
| Electrical Warning Plate   |                                    | <b>1492-EWPL4</b>            |                     | 20                  |   | <b>1492-EWPL4</b>            |                     | 20                  |  | <b>1492-EWPL4</b>            |                     | 20                  |
| <b>Marking Systems</b>   |                                    |                              |                     |                     |   |                              |                     |                     |  |                              |                     |                     |
| Snap-In Marker Cards   |                                    | <b>1492-M3X12</b> (120/card) |                     | 5                   |   | <b>1492-M3X12</b> (120/card) |                     | 5                   |  | <b>1492-M3X12</b> (120/card) |                     | 5                   |
| Snap-In Marker Cards   |                                    | <b>1492-M3X5</b> (100/card)  |                     | 5                   |   | <b>1492-M3X5</b> (100/card)  |                     | 5                   |  | <b>1492-M3X5</b> (100/card)  |                     | 5                   |

