

Product Details and Certifications

Cross Reference RA Part Number: 1492-EBL3 A

 Product: **1492-EBL3**

Description: 1492 Terminal Block, End Barrier, Gray (Standard)



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

SELECTION

1492 Accessory

Spring-Clamp Connection Terminal Blocks

Standard Feed-Through Blocks

	1492-L3				1492-L3T				1492-L3Q							
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.																
Specifications	<i>Feed-through terminal block</i>								<i>Feed-through terminal block with 3 connection points, 2 on one side</i>				<i>Feed-through terminal block with 2 points on each side</i>			
Certifications		CSA	IEC	ATEX		CSA	IEC	ATEX		CSA	IEC	ATEX				
Voltage Rating	600V AC/DC		800V AC/DC	550V AC/DC	600V AC/DC		800V AC/DC	550V AC/DC	600V AC/DC		800V AC/DC	550V AC/DC				
Maximum Current	25 A	27 A	24 A	21 A	25 A	27 A	24 A	21 A	25 A	27 A	24 A	21 A				
Wire Range (Rated Cross Section)	#30... 12 AWG	#26... 12 AWG	2.5 mm ²	2.5 mm ² (20...12 AWG)	#30... 12 AWG	#26... 12 AWG	2.5 mm ²	2.5 mm ² (20...12 AWG)	#30... 12 AWG	#26... 12 AWG	2.5 mm ²	2.5 mm ² (20...12 AWG)				
Wire Strip Length	0.39 in. (10 mm)				0.39 in. (10 mm)				0.39 in. (10 mm)							
Density	59 pcs/ft (196 pcs/m)				59 pcs/ft (196 pcs/m)				59 pcs/ft (196 pcs/m)							
Housing Temperature Range	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)							
Short-Circuit Current Rating (SCCR)	See page 12-78															
Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.								
Color	Grey	1492-L3	100	1492-L3T	100	1492-L3Q	100									
	Red	1492-L3-RE	100	1492-L3T-RE	100	1492-L3Q-RE	100									
	Blue	1492-L3-B	100	1492-L3T-B	100	1492-L3Q-B	100									
	Black	1492-L3-BL	100	1492-L3T-BL	100	1492-L3Q-BL	100									
	Green	1492-L3-G	100	1492-L3T-G	100	1492-L3Q-G	100									
	Yellow	1492-L3-Y	100	1492-L3T-Y	100	1492-L3Q-Y	100									
	Orange	1492-L3-OR	100	1492-L3T-OR	100	1492-L3Q-OR	100									
	Brown	1492-L3-BR	100	1492-L3T-BR	100	1492-L3Q-BR	100									
	White	1492-L3-W	100	1492-L3T-W	100	1492-L3Q-W	100									
Accessories	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.										
Mounting Rails																
1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10	199-DR1	10										
1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10	1492-DR5	10										
1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6	2	1492-DR6	2	1492-DR6	2										
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2	1492-DR7	2										
End Barriers	Grey	1492-EBL3	50	1492-EBL3T	50	1492-EBL3Q	50									
	Blue	1492-EBL3-B	50	1492-EBL3T-B	50	1492-EBL3Q-B	50									
	Yellow	1492-EBL3-Y	50	1492-EBL3T-Y	50	1492-EBL3Q-Y	50									
End Anchors and Retainers																
Screwless End Retainer	1492-ERL35	20	1492-ERL35	20	1492-ERL35	20										
DIN Rail — Normal Duty	1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100										
DIN Rail — Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50										
Jumpers																
Plug-in Center Jumper — 50-Pole	1492-CJK5-50	10	1492-CJK5-50	10	1492-CJK5-50	10										
Plug-in Center Jumper — 10-Pole	1492-CJK5-10	20	1492-CJK5-10	20	1492-CJK5-10	20										
Plug-in Center Jumper — 9-Pole	1492-CJK5-9	20	1492-CJK5-9	20	1492-CJK5-9	20										
Plug-in Center Jumper — 8-Pole	1492-CJK5-8	20	1492-CJK5-8	20	1492-CJK5-8	20										
Plug-in Center Jumper — 7-Pole	1492-CJK5-7	20	1492-CJK5-7	20	1492-CJK5-7	20										
Plug-in Center Jumper — 6-Pole	1492-CJK5-6	20	1492-CJK5-6	20	1492-CJK5-6	20										
Plug-in Center Jumper — 5-Pole	1492-CJK5-5	20	1492-CJK5-5	20	1492-CJK5-5	20										
Plug-in Center Jumper — 4-Pole	1492-CJK5-4	60	1492-CJK5-4	60	1492-CJK5-4	60										
Plug-in Center Jumper — 3-Pole	1492-CJK5-3	60	1492-CJK5-3	60	1492-CJK5-3	60										
Plug-in Center Jumper — 2-Pole	1492-CJK5-2	60	1492-CJK5-2	60	1492-CJK5-2	60										
Other Accessories																
Reducing Sleeves #30...#24 AWG (0.13...0.2 mm ²) White	1492-PSL3-2	100	1492-PSL3-2	100	1492-PSL3-2	100										
Reducing Sleeves #22...#20 AWG (0.25...0.5 mm ²) Grey	1492-PSL3-5	100	1492-PSL3-5	100	1492-PSL3-5	100										
Reducing Sleeves #18 AWG (0.75...1.0 mm ²) Dark Grey	1492-PSL3-10	100	1492-PSL3-10	100	1492-PSL3-10	100										
Test Plug	1492-TP23	20	1492-TP23	20	1492-TP23	20										
Test Plug (Stackable)	1492-TPL5	25	1492-TPL5	25	1492-TPL5	25										
Electrical Warning Plate	1492-EWPL5	20	1492-EWPL5	20	1492-EWPL5	20										
Marking Systems																
Snap-In Marker Cards	1492-M5X10 (144/card)	5	1492-M5X10 (144/card)	5	1492-M5X10 (144/card)	5										
Snap-In Marker Cards	1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5										
Hinged Marker Cards	1492-MH5X10 (96/card)	5	1492-MH5X10 (96/card)	5	1492-MH5X10 (96/card)	5										
Hinged Marker Cards	1492-MH5X15 (96/card)	5	1492-MH5X15 (96/card)	5	1492-MH5X15 (96/card)	5										