

# Product Details and Certifications

**Cross Reference RA Part Number: 1492-EBL3T-Y A**

 **Product: 1492-EBL3T-Y**

Description: 1492 Terminal Block, End Barrier, Yellow



Representative Photo Only (actual product may vary based on configuration sections)

## ***ACCESSORY SELECTION***

---

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

## ***SELECTION***

---

1492 Accessory

# Spring-Clamp Connection Terminal Blocks

## Standard Feed-Through Blocks

	1492-L3				1492-L3T				1492-L3Q			
Dimensions are not intended to be used for manufacturing purposes. <b>Note:</b> Height dimension is measured from top of rail to top of terminal block.												
<b>Specifications</b>	<i>Feed-through terminal block</i>				<i>Feed-through terminal block with 3 connection points, 2 on one side</i>				<i>Feed-through terminal block with 2 points on each side</i>			
<b>Certifications</b>		<b>CSA</b>	<b>IEC</b>	<b>ATEX</b>		<b>CSA</b>	<b>IEC</b>	<b>ATEX</b>		<b>CSA</b>	<b>IEC</b>	<b>ATEX</b>
<b>Voltage Rating</b>	600V AC/DC		800V AC/DC	550V AC/DC	600V AC/DC		800V AC/DC	550V AC/DC	600V AC/DC		800V AC/DC	550V AC/DC
<b>Maximum Current</b>	25 A	27 A	24 A	21 A	25 A	27 A	24 A	21 A	25 A	27 A	24 A	21 A
<b>Wire Range (Rated Cross Section)</b>	#30... 12 AWG	#26... 12 AWG	2.5 mm <sup>2</sup>	2.5 mm <sup>2</sup> (20...12 AWG)	#30... 12 AWG	#26... 12 AWG	2.5 mm <sup>2</sup>	2.5 mm <sup>2</sup> (20...12 AWG)	#30... 12 AWG	#26... 12 AWG	2.5 mm <sup>2</sup>	2.5 mm <sup>2</sup> (20...12 AWG)
<b>Wire Strip Length</b>	0.39 in. (10 mm)				0.39 in. (10 mm)				0.39 in. (10 mm)			
<b>Density</b>	59 pcs/ft (196 pcs/m)				59 pcs/ft (196 pcs/m)				59 pcs/ft (196 pcs/m)			
<b>Housing Temperature Range</b>	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)			
<b>Short-Circuit Current Rating (SCCR)</b>	See page 12-78											
<b>Terminal Blocks</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>				
<b>Color</b>	Grey	<b>1492-L3</b>	100	<b>1492-L3T</b>	100	<b>1492-L3Q</b>	100					
	Red	<b>1492-L3-RE</b>	100	<b>1492-L3T-RE</b>	100	<b>1492-L3Q-RE</b>	100					
	Blue	<b>1492-L3-B</b>	100	<b>1492-L3T-B</b>	100	<b>1492-L3Q-B</b>	100					
	Black	<b>1492-L3-BL</b>	100	<b>1492-L3T-BL</b>	100	<b>1492-L3Q-BL</b>	100					
	Green	<b>1492-L3-G</b>	100	<b>1492-L3T-G</b>	100	<b>1492-L3Q-G</b>	100					
	Yellow	<b>1492-L3-Y</b>	100	<b>1492-L3T-Y</b>	100	<b>1492-L3Q-Y</b>	100					
	Orange	<b>1492-L3-OR</b>	100	<b>1492-L3T-OR</b>	100	<b>1492-L3Q-OR</b>	100					
	Brown	<b>1492-L3-BR</b>	100	<b>1492-L3T-BR</b>	100	<b>1492-L3Q-BR</b>	100					
	White	<b>1492-L3-W</b>	100	<b>1492-L3T-W</b>	100	<b>1492-L3Q-W</b>	100					
<b>Accessories</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>						
<b>Mounting Rails</b>												
1 m Symmetrical DIN (Steel)	<b>199-DR1</b>	10	<b>199-DR1</b>	10	<b>199-DR1</b>	10						
1 m Symmetrical DIN (Aluminum)	<b>1492-DR5</b>	10	<b>1492-DR5</b>	10	<b>1492-DR5</b>	10						
1 m Hi-Rise Sym. DIN (Aluminum)	<b>1492-DR6</b>	2	<b>1492-DR6</b>	2	<b>1492-DR6</b>	2						
1 m Angled Hi-Rise Sym. DIN (Steel)	<b>1492-DR7</b>	2	<b>1492-DR7</b>	2	<b>1492-DR7</b>	2						
<b>End Barriers</b>	Grey	<b>1492-EBL3</b>	50	<b>1492-EBL3T</b>	50	<b>1492-EBL3Q</b>	50					
	Blue	<b>1492-EBL3-B</b>	50	<b>1492-EBL3T-B</b>	50	<b>1492-EBL3Q-B</b>	50					
	Yellow	<b>1492-EBL3-Y</b>	50	<b>1492-EBL3T-Y</b>	50	<b>1492-EBL3Q-Y</b>	50					
<b>End Anchors and Retainers</b>												
Screwless End Retainer	<b>1492-ERL35</b>	20	<b>1492-ERL35</b>	20	<b>1492-ERL35</b>	20						
<b>DIN Rail — Normal Duty</b>	<b>1492-EAJ35</b>	100	<b>1492-EAJ35</b>	100	<b>1492-EAJ35</b>	100						
<b>DIN Rail — Heavy Duty</b>	<b>1492-EAHJ35</b>	50	<b>1492-EAHJ35</b>	50	<b>1492-EAHJ35</b>	50						
<b>Jumpers</b>												
Plug-in Center Jumper — 50-Pole	<b>1492-CJK5-50</b>	10	<b>1492-CJK5-50</b>	10	<b>1492-CJK5-50</b>	10						
Plug-in Center Jumper — 10-Pole	<b>1492-CJK5-10</b>	20	<b>1492-CJK5-10</b>	20	<b>1492-CJK5-10</b>	20						
Plug-in Center Jumper — 9-Pole	<b>1492-CJK5-9</b>	20	<b>1492-CJK5-9</b>	20	<b>1492-CJK5-9</b>	20						
Plug-in Center Jumper — 8-Pole	<b>1492-CJK5-8</b>	20	<b>1492-CJK5-8</b>	20	<b>1492-CJK5-8</b>	20						
Plug-in Center Jumper — 7-Pole	<b>1492-CJK5-7</b>	20	<b>1492-CJK5-7</b>	20	<b>1492-CJK5-7</b>	20						
Plug-in Center Jumper — 6-Pole	<b>1492-CJK5-6</b>	20	<b>1492-CJK5-6</b>	20	<b>1492-CJK5-6</b>	20						
Plug-in Center Jumper — 5-Pole	<b>1492-CJK5-5</b>	20	<b>1492-CJK5-5</b>	20	<b>1492-CJK5-5</b>	20						
Plug-in Center Jumper — 4-Pole	<b>1492-CJK5-4</b>	60	<b>1492-CJK5-4</b>	60	<b>1492-CJK5-4</b>	60						
Plug-in Center Jumper — 3-Pole	<b>1492-CJK5-3</b>	60	<b>1492-CJK5-3</b>	60	<b>1492-CJK5-3</b>	60						
Plug-in Center Jumper — 2-Pole	<b>1492-CJK5-2</b>	60	<b>1492-CJK5-2</b>	60	<b>1492-CJK5-2</b>	60						
<b>Other Accessories</b>												
Reducing Sleeves #30...#24 AWG (0.13...0.2 mm <sup>2</sup> ) White	<b>1492-PSL3-2</b>	100	<b>1492-PSL3-2</b>	100	<b>1492-PSL3-2</b>	100						
Reducing Sleeves #22...#20 AWG (0.25...0.5 mm <sup>2</sup> ) Grey	<b>1492-PSL3-5</b>	100	<b>1492-PSL3-5</b>	100	<b>1492-PSL3-5</b>	100						
Reducing Sleeves #18 AWG (0.75...1.0 mm <sup>2</sup> ) Dark Grey	<b>1492-PSL3-10</b>	100	<b>1492-PSL3-10</b>	100	<b>1492-PSL3-10</b>	100						
<b>Test Plug</b>	<b>1492-TP23</b>	20	<b>1492-TP23</b>	20	<b>1492-TP23</b>	20						
<b>Test Plug (Stackable)</b>	<b>1492-TPL5</b>	25	<b>1492-TPL5</b>	25	<b>1492-TPL5</b>	25						
<b>Electrical Warning Plate</b>	<b>1492-EWPL5</b>	20	<b>1492-EWPL5</b>	20	<b>1492-EWPL5</b>	20						
<b>Marking Systems</b>												
Snap-In Marker Cards	<b>1492-M5X10</b> (144/card)	5	<b>1492-M5X10</b> (144/card)	5	<b>1492-M5X10</b> (144/card)	5						
Snap-In Marker Cards	<b>1492-M5X5</b> (200/card)	5	<b>1492-M5X5</b> (200/card)	5	<b>1492-M5X5</b> (200/card)	5						
Hinged Marker Cards	<b>1492-MH5X10</b> (96/card)	5	<b>1492-MH5X10</b> (96/card)	5	<b>1492-MH5X10</b> (96/card)	5						
Hinged Marker Cards	<b>1492-MH5X15</b> (96/card)	5	<b>1492-MH5X15</b> (96/card)	5	<b>1492-MH5X15</b> (96/card)	5						

