

Product Details and Certifications

Cross Reference RA Part Number: 1492-EBL3T A

 **Product: 1492-EBL3T**

Description: 1492 Terminal Block, End Barrier, Gray (Standard)



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION




Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

SELECTION

1492 Accessory

Spring-Clamp Connection Terminal Blocks

Standard Feed-Through Blocks

	1492-L3	1492-L3T	1492-L3Q	
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.				
Specifications	<i>Feed-through terminal block</i>		<i>Feed-through terminal block with 3 connection points, 2 on one side</i>	
Certifications	CSA IEC ATEX	CSA IEC ATEX	CSA IEC ATEX	
Voltage Rating	600V AC/DC 800V AC/DC 550V AC/DC		600V AC/DC 800V AC/DC 550V AC/DC	
Maximum Current	25 A 27 A 24 A		25 A 27 A 24 A	
Wire Range (Rated Cross Section)	#30...12 AWG #26...12 AWG 2.5 mm ² (20...12 AWG)		#30...12 AWG #26...12 AWG 2.5 mm ² (20...12 AWG)	
Wire Strip Length	0.39 in. (10 mm)			
Density	59 pcs/ft (196 pcs/m)			
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			
Short-Circuit Current Rating (SCCR)	See page 12-78			
Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Color	1492-L3	100	1492-L3T	100
Grey	1492-L3	100	1492-L3T	100
Red	1492-L3-RE	100	1492-L3T-RE	100
Blue	1492-L3-B	100	1492-L3T-B	100
Black	1492-L3-BL	100	1492-L3T-BL	100
Green	1492-L3-G	100	1492-L3T-G	100
Yellow	1492-L3-Y	100	1492-L3T-Y	100
Orange	1492-L3-OR	100	1492-L3T-OR	100
Brown	1492-L3-BR	100	1492-L3T-BR	100
White	1492-L3-W	100	1492-L3T-W	100
Accessories	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Mounting Rails				
1 m Symmetrical DIN (Steel)	199-DR1	10	199-DR1	10
1 m Symmetrical DIN (Aluminum)	1492-DR5	10	1492-DR5	10
1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6	2	1492-DR6	2
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7	2	1492-DR7	2
End Barriers	1492-EBL3	50	1492-EBL3T	50
Grey	1492-EBL3	50	1492-EBL3T	50
Blue	1492-EBL3-B	50	1492-EBL3T-B	50
Yellow	1492-EBL3-Y	50	1492-EBL3T-Y	50
End Anchors and Retainers				
Screwless End Retainer	1492-ERL35	20	1492-ERL35	20
DIN Rail — Normal Duty	1492-EAJ35	100	1492-EAJ35	100
DIN Rail — Heavy Duty	1492-EAHJ35	50	1492-EAHJ35	50
Jumpers				
Plug-in Center Jumper — 50-Pole	1492-CJK5-50	10	1492-CJK5-50	10
Plug-in Center Jumper — 10-Pole	1492-CJK5-10	20	1492-CJK5-10	20
Plug-in Center Jumper — 9-Pole	1492-CJK5-9	20	1492-CJK5-9	20
Plug-in Center Jumper — 8-Pole	1492-CJK5-8	20	1492-CJK5-8	20
Plug-in Center Jumper — 7-Pole	1492-CJK5-7	20	1492-CJK5-7	20
Plug-in Center Jumper — 6-Pole	1492-CJK5-6	20	1492-CJK5-6	20
Plug-in Center Jumper — 5-Pole	1492-CJK5-5	20	1492-CJK5-5	20
Plug-in Center Jumper — 4-Pole	1492-CJK5-4	60	1492-CJK5-4	60
Plug-in Center Jumper — 3-Pole	1492-CJK5-3	60	1492-CJK5-3	60
Plug-in Center Jumper — 2-Pole	1492-CJK5-2	60	1492-CJK5-2	60
Other Accessories				
Reducing Sleeves #30...#24 AWG (0.13...0.2 mm ²) White	1492-PSL3-2	100	1492-PSL3-2	100
Reducing Sleeves #22...#20 AWG (0.25...0.5 mm ²) Grey	1492-PSL3-5	100	1492-PSL3-5	100
Reducing Sleeves #18 AWG (0.75...1.0 mm ²) Dark Grey	1492-PSL3-10	100	1492-PSL3-10	100
Test Plug	1492-TP23	20	1492-TP23	20
Test Plug (Stackable)	1492-TPL5	25	1492-TPL5	25
Electrical Warning Plate	1492-EWPL5	20	1492-EWPL5	20
Marking Systems				
Snap-In Marker Cards	1492-M5X10 (144/card)	5	1492-M5X10 (144/card)	5
Snap-In Marker Cards	1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5
Hinged Marker Cards	1492-MH5X10 (96/card)	5	1492-MH5X10 (96/card)	5
Hinged Marker Cards	1492-MH5X15 (96/card)	5	1492-MH5X15 (96/card)	5

