

Product Details and Certifications

Cross Reference RA Part Number: 1492-EBL4 A

 **Product: 1492-EBL4**

Description: 1492 Terminal Block, End Barrier, Gray (Standard), Qty. 50



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

SELECTION

1492 Accessory

Spring-Clamp Connection Terminal Blocks

Standard Feed-Through Blocks

	1492-L4				1492-L4T				1492-L4Q			
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.												
Specifications	<i>Feed-through terminal block</i>				<i>Feed-through terminal block with 3 connection points, 2 on one side</i>				<i>Feed-through terminal block with 2 connection points on each side</i>			
Certifications												
Voltage Rating	600V AC/DC		800V AC/DC	550V AC/DC	600V AC/DC		800V AC/DC	550V AC/DC	600V AC/DC		800V AC/DC	550V AC/DC
Maximum Current	33 A	35 A	32 A	28 A	33 A	35 A	32 A	28 A	33 A	35 A	32 A	28 A
Wire Range (Rated Cross Section)	#26...10 AWG		4 mm ²	4 mm ² (20...10 AWG)	#26...10 AWG		4 mm ²	4 mm ² (20...10 AWG)	#26...10 AWG		4 mm ²	4 mm ² (20...10 AWG)
Wire Strip Length	0.47 in. (12 mm)				0.47 in. (12 mm)				0.47 in. (12 mm)			
Density	49 pcs/ft (163 pcs/m)				49 pcs/ft (163 pcs/m)				49 pcs/ft (163 pcs/m)			
Housing Temperature Range	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)			
Short-Circuit Current Rating	See page 12-78											
Terminal Blocks		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.
Color	Grey	1492-L4	50		1492-L4T	50		1492-L4Q	50		1492-L4Q-RE	50
	Red	1492-L4-RE	50		1492-L4T-RE	50		1492-L4Q-RE	50		1492-L4Q-B	50
	Blue	1492-L4-B	50		1492-L4T-B	50		1492-L4Q-B	50		1492-L4Q-BL	50
	Black	1492-L4-BL	50		1492-L4T-BL	50		1492-L4Q-BL	50		1492-L4Q-G	50
	Green	1492-L4-G	50		1492-L4T-G	50		1492-L4Q-G	50		1492-L4Q-Y	50
	Yellow	1492-L4-Y	50		1492-L4T-Y	50		1492-L4Q-Y	50		1492-L4Q-OR	50
	Orange	1492-L4-OR	50		1492-L4T-OR	50		1492-L4Q-OR	50		1492-L4Q-BR	50
	Brown	1492-L4-BR	50		1492-L4T-BR	50		1492-L4Q-BR	50		1492-L4Q-W	50
	White	1492-L4-W	50		1492-L4T-W	50		1492-L4Q-W	50			
Accessories		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.
Mounting Rails												
1 m Symmetrical DIN (Steel)		199-DR1	10		199-DR1	10		199-DR1	10		199-DR1	10
1 m Symmetrical DIN (Aluminum)		1492-DR5	10		1492-DR5	10		1492-DR5	10		1492-DR5	10
1 m Hi-Rise Sym. DIN (Aluminum)		1492-DR6	2		1492-DR6	2		1492-DR6	2		1492-DR6	2
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7	2		1492-DR7	2		1492-DR7	2		1492-DR7	2
End Barriers	Grey	1492-EBL4	50		1492-EBL4T	50		1492-EBL4Q	50		1492-EBL4Q-B	50
	Blue	1492-EBL4-B	50		1492-EBL4T-B	50		1492-EBL4Q-B	50		1492-EBL4Q-Y	50
	Yellow	1492-EBL4-Y	50		1492-EBL4T-Y	50		1492-EBL4Q-Y	50			
End Anchors and Retainers												
Screwless End Retainer		1492-ERL35	20		1492-ERL35	20		1492-ERL35	20		1492-ERL35	20
DIN Rail — Normal Duty		1492-EAJ35	100		1492-EAJ35	100		1492-EAJ35	100		1492-EAJ35	100
DIN Rail — Heavy Duty		1492-EAHJ35	50		1492-EAHJ35	50		1492-EAHJ35	50		1492-EAHJ35	50
Jumpers:												
Plug-in Center Jumper — 10-Pole		1492-CJK6-10	20		1492-CJK6-10	20		1492-CJK6-10	20		1492-CJK6-10	20
Plug-in Center Jumper — 9-Pole		1492-CJK6-9	20		1492-CJK6-9	20		1492-CJK6-9	20		1492-CJK6-9	20
Plug-in Center Jumper — 8-Pole		1492-CJK6-8	20		1492-CJK6-8	20		1492-CJK6-8	20		1492-CJK6-8	20
Plug-in Center Jumper — 7-Pole		1492-CJK6-7	20		1492-CJK6-7	20		1492-CJK6-7	20		1492-CJK6-7	20
Plug-in Center Jumper — 6-Pole		1492-CJK6-6	20		1492-CJK6-6	20		1492-CJK6-6	20		1492-CJK6-6	20
Plug-in Center Jumper — 5-Pole		1492-CJK6-5	20		1492-CJK6-5	20		1492-CJK6-5	20		1492-CJK6-5	20
Plug-in Center Jumper — 4-Pole		1492-CJK6-4	60		1492-CJK6-4	60		1492-CJK6-4	60		1492-CJK6-4	60
Plug-in Center Jumper — 3-Pole		1492-CJK6-3	60		1492-CJK6-3	60		1492-CJK6-3	60		1492-CJK6-3	60
Plug-in Center Jumper — 2-Pole		1492-CJK6-2	60		1492-CJK6-2	60		1492-CJK6-2	60		1492-CJK6-2	60
Other Accessories												
Reducing Sleeves #26...#24 AWG (0.13...0.2 mm ²) White		1492-PSL4-2	100		1492-PSL4-2	100		1492-PSL4-2	100		1492-PSL4-2	100
Reducing Sleeves #20...#22 AWG (0.25...0.5 mm ²) Grey		1492-PSL4-5	100		1492-PSL4-5	100		1492-PSL4-5	100		1492-PSL4-5	100
Reducing Sleeves #18 AWG (0.75...1.0 mm ²) Dark Grey		1492-PSL4-10	100		1492-PSL4-10	100		1492-PSL4-10	100		1492-PSL4-10	100
Test Plug		1492-TP23	20		1492-TP23	20		1492-TP23	20		1492-TP23	20
Test Plug (Stackable)		1492-TPL6	25		1492-TPL6	25		1492-TPL6	25		1492-TPL6	25
Electrical Warning Plate		1492-EWPL6	20		1492-EWPL6	20		1492-EWPL6	20		1492-EWPL6	20
Marking Systems												
Snap-In Marker Cards		1492-M6X10 (120/card)	5		1492-M6X10 (120/card)	5		1492-M6X10 (120/card)	5		1492-M6X10 (120/card)	5
Snap-In Marker Cards		1492-M6X5 (200/card)	5		1492-M6X5 (200/card)	5		1492-M6X5 (200/card)	5		1492-M6X5 (200/card)	5
Hinged Marker Cards		1492-MH6X12 (80/card)	5		1492-MH6X12 (80/card)	5		1492-MH6X12 (80/card)	5		1492-MH6X12 (80/card)	5

