

Product Details and Certifications

Cross Reference RA Part Number: 1492-EBL6-Y A



Product: 1492-EBL6-Y

Description: 1492 Terminal Block, End Barrier, Yellow, Qty. 50



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

SELECTION

1492 Accessory

Spring-Clamp Connection Terminal Blocks

Standard Feed-Through Blocks

	1492-L6				1492-L6T				1492-L10									
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.																		
	Specifications				<i>Feed-through terminal block</i>				<i>Feed-through terminal block with 2 connection points on one side</i>				<i>Feed-through terminal block</i>					
Certifications	CSA IEC ATEX				CSA IEC ATEX				CSA IEC ATEX									
Voltage Rating	600V AC/DC 800V AC/DC 550V AC/DC				600V AC/DC 800V AC/DC 550V AC/DC				600V AC/DC 800V AC/DC 550V AC/DC									
Maximum Current	50 A 41 A 36 A				50 A 41 A 36 A				60 A 55 A 57 A 50 A									
Wire Range (Rated Cross Section)	#22...8 AWG #20...8 AWG 6 mm ² 6 mm ² (20...8 AWG)				#22...8 AWG #20...8 AWG 6 mm ² 6 mm ² (#20...10 AWG)				#16...6 AWG 10 mm ² 10 mm ² (16...8 AWG)									
Wire Strip Length	0.51 in. (13 mm)				0.51 in. (13 mm)				0.70 in. (18 mm)									
Density	37 pcs/ft (123 pcs/m)				37 pcs/ft(123 pcs/m)				30 pcs/ft (99 pcs/m)									
Housing Temperature Range	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)									
Short-Circuit Current Rating	See page 12-78																	
Terminal Blocks	Cat. No.			Pkg Qty.			Cat. No.			Pkg Qty.			Cat. No.			Pkg Qty.		
Color	Grey	1492-L6		50	1492-L6T	50		1492-L10	25									
	Red	1492-L6-RE		50	1492-L6T-RE	50		1492-L10-RE	25									
	Blue	1492-L6-B		50	1492-L6T-B	50		1492-L10-B	25									
	Black	1492-L6-BL		50	1492-L6T-BL	50		1492-L10-BL	25									
	Green	1492-L6-G		50	1492-L6T-G	50		1492-L10-G	25									
	Yellow	1492-L6-Y		50	1492-L6T-Y	50		1492-L10-Y	25									
	Orange	1492-L6-OR		50	1492-L6T-OR	50		1492-L10-OR	25									
	Brown	1492-L6-BR		50	1492-L6T-BR	50		1492-L10-BR	25									
	White	1492-L6-W		50	1492-L6T-W	50		1492-L10-W	25									
Accessories	Cat. No.			Pkg Qty.			Cat. No.			Pkg Qty.			Cat. No.			Pkg Qty.		
Mounting Rails																		
1 m Symmetrical DIN (Steel)	199-DR1			10	199-DR1	10		199-DR1	10									
1 m Symmetrical DIN (Aluminum)	1492-DR5			10	1492-DR5	10		1492-DR5	10									
1 m Hi-Rise Sym. DIN (Aluminum)	1492-DR6			2	1492-DR6	2		1492-DR6	2									
1 m Angled Hi-Rise Sym. DIN (Steel)	1492-DR7			2	1492-DR7	2		1492-DR7	2									
End Barriers	Grey	1492-EBL6		50	1492-EBL6T	50		1492-EBL10	20									
	Blue	1492-EBL6-B		50	1492-EBL6T-B	50		1492-EBL10-B	20									
	Yellow	1492-EBL6-Y		50	1492-EBL6T-Y	50		1492-EBL10-Y	20									
End Anchors and Retainers																		
Screwless End Retainer	1492-ERL35			20	1492-ERL35	20		1492-ERL35	20									
DIN Rail — Normal Duty	1492-EAJ35			100	1492-EAJ35	100		1492-EAJ35	100									
DIN Rail — Heavy Duty	1492-EAHJ35			50	1492-EAHJ35	50		1492-EAHJ35	50									
Jumpers																		
Plug-in Center Jumper — 32-Pole	1492-CJL8-32			10	1492-CJL8-32	10		—	—									
Plug-in Center Jumper — 4-Pole	1492-CJL8-4			60	1492-CJL8-4	60		—	—									
Plug-in Center Jumper — 3-Pole	1492-CJL8-3			60	1492-CJL8-3	60		—	—									
Plug-in Center Jumper — 2-Pole	1492-CJL8-2			60	1492-CJL8-2	60		1492-CJL10-2	25									
Other Accessories																		
Test Plug	—			—	—	—		1492-TP23	20									
Test Plug (Stackable)	1492-TPL8			25	1492-TPL8	25		—	—									
Electrical Warning Plate	1492-EWPL8			20	1492-EWPL8	20		1492-EWPL10	20									
Marking Systems																		
Snap-In Marker Cards*	1492-M6X12 (120/card)			5	1492-M6X12 (120/card)	5		1492-M6X12 (120/card)	5									
Snap-In Marker Cards	1492-MR8X12 (84/card)			5	1492-M8X5 (160/card)	5		1492-M8X5 (160/card)	5									
Hinged Marker Cards	1492-MH6X12 (80/card)			5	1492-MH6X12 (80/card)	5		1492-MH5X15 (96/card)	5									

* May only be mounted in terminal block corner marking positions.