

Product Details and Certifications

Cross Reference RA Part Number: 1492-EBL6 A

 **Product: 1492-EBL6**

Description: 1492 Terminal Block, End Barrier, Gray (Standard), Qty. 50



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

SELECTION

1492 Accessory

Spring-Clamp Connection Terminal Blocks

Standard Feed-Through Blocks

	1492-L6				1492-L6T				1492-L10			
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.												
	Specifications <i>Feed-through terminal block</i>				<i>Feed-through terminal block with 2 connection points on one side</i>				<i>Feed-through terminal block</i>			
Certifications		CSA	IEC	ATEX		CSA	IEC	ATEX		CSA	IEC	ATEX
Voltage Rating	600V AC/DC			800V AC/DC	600V AC/DC			800V AC/DC	600V AC/DC			800V AC/DC
Maximum Current	50 A		41 A	36 A	50 A		41 A	36 A	60 A	55 A	57 A	50 A
Wire Range (Rated Cross Section)	#22...8 AWG	#20...8 AWG	6 mm ²	6 mm ² (20...8 AWG)	#22...8 AWG	#20...8 AWG	6 mm ²	6 mm ² (#20...10 AWG)	#16...6 AWG	10 mm ²	10 mm ² (16...8 AWG)	10 mm ² (16...8 AWG)
Wire Strip Length	0.51 in. (13 mm)				0.51 in. (13 mm)				0.70 in. (18 mm)			
Density	37 pcs/ft (123 pcs/m)				37 pcs/ft(123 pcs/m)				30 pcs/ft (99 pcs/m)			
Housing Temperature Range	-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)				-58...+248 °F (-50...+120 °C)			
Short-Circuit Current Rating	See page 12-78											
Terminal Blocks		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.
Color	Grey	1492-L6	50		1492-L6T	50		1492-L10	25			
	Red	1492-L6-RE	50		1492-L6T-RE	50		1492-L10-RE	25			
	Blue	1492-L6-B	50		1492-L6T-B	50		1492-L10-B	25			
	Black	1492-L6-BL	50		1492-L6T-BL	50		1492-L10-BL	25			
	Green	1492-L6-G	50		1492-L6T-G	50		1492-L10-G	25			
	Yellow	1492-L6-Y	50		1492-L6T-Y	50		1492-L10-Y	25			
	Orange	1492-L6-OR	50		1492-L6T-OR	50		1492-L10-OR	25			
	Brown	1492-L6-BR	50		1492-L6T-BR	50		1492-L10-BR	25			
	White	1492-L6-W	50		1492-L6T-W	50		1492-L10-W	25			
Accessories		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.
Mounting Rails												
1 m Symmetrical DIN (Steel)		199-DR1	10		199-DR1	10		199-DR1	10			
1 m Symmetrical DIN (Aluminum)		1492-DR5	10		1492-DR5	10		1492-DR5	10			
1 m Hi-Rise Sym. DIN (Aluminum)		1492-DR6	2		1492-DR6	2		1492-DR6	2			
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7	2		1492-DR7	2		1492-DR7	2			
End Barriers	Grey	1492-EBL6	50		1492-EBL6T	50		1492-EBL10	20			
	Blue	1492-EBL6-B	50		1492-EBL6T-B	50		1492-EBL10-B	20			
	Yellow	1492-EBL6-Y	50		1492-EBL6T-Y	50		1492-EBL10-Y	20			
End Anchors and Retainers												
Screwless End Retainer		1492-ERL35	20		1492-ERL35	20		1492-ERL35	20			
DIN Rail — Normal Duty		1492-EAJ35	100		1492-EAJ35	100		1492-EAJ35	100			
DIN Rail — Heavy Duty		1492-EAHJ35	50		1492-EAHJ35	50		1492-EAHJ35	50			
Jumpers												
Plug-in Center Jumper — 32-Pole		1492-CJL8-32	10		1492-CJL8-32	10		—	—			
Plug-in Center Jumper — 4-Pole		1492-CJL8-4	60		1492-CJL8-4	60		—	—			
Plug-in Center Jumper — 3-Pole		1492-CJL8-3	60		1492-CJL8-3	60		—	—			
Plug-in Center Jumper — 2-Pole		1492-CJL8-2	60		1492-CJL8-2	60		1492-CJL10-2	25			
Other Accessories												
Test Plug		—	—		—	—		1492-TP23	20			
Test Plug (Stackable)		1492-TPL8	25		1492-TPL8	25		—	—			
Electrical Warning Plate		1492-EWPL8	20		1492-EWPL8	20		1492-EWPL10	20			
Marking Systems												
Snap-In Marker Cards*		1492-M6X12 (120/card)	5		1492-M6X12 (120/card)	5		1492-M6X12 (120/card)	5			
Snap-In Marker Cards		1492-MR8X12 (84/card)	5		1492-M8X5 (160/card)	5		1492-M8X5 (160/card)	5			
Hinged Marker Cards		1492-MH6X12 (80/card)	5		1492-MH6X12 (80/card)	5		1492-MH5X15 (96/card)	5			

* May only be mounted in terminal block corner marking positions.