

# Product Details and Certifications

**Cross Reference RA Part Number: 1492-EBLC3 A**



**Product: 1492-EBLC3**

Description: 1492 Terminal Block, End Barrier, Gray (Standard), Qty. 20



Representative Photo Only (actual product may vary based on configuration sections)

## ***ACCESSORY SELECTION***

---

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

## ***SELECTION***

---

1492 Accessory

# Spring-Clamp Connection Terminal Blocks

## Plug-in Connection Blocks

	1492-LC3			1492-LDC3		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.						
<b>Specifications</b>	Feed-through terminal block with plug in comb connection on one side.			Two Circuit terminal block with plug in comb connection on one side of each circuit		
Certifications		CSA	IEC		CSA	IEC
Voltage Rating	300V AC/DC		250V AC/DC	300V AC/DC		250V AC/DC
Maximum Current	10 A		16 A	10 A		16 A
Wire Range (Rated Cross Section)	#26...12 AWG		2.5 mm <sup>2</sup>	#26...14 AWG		2.5 mm <sup>2</sup>
Wire Strip Length	0.39 in. (10 mm)			0.39 in. (10 mm)		
Density	59 pcs/ft (196 pcs/m)			59 pcs/ft (196 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)		
<b>Terminal Blocks</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>	
Color	Grey	<b>1492-LC3</b>	50	1492-LDC3	50	
<b>Plug Connection Strips</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>	
Color/Quantity	Black/2-Pole	<b>1492-QP5-2</b>	100	<b>1492-QP5-2</b>	100	
	Black/3-Pole	<b>1492-QP5-3</b>	100	<b>1492-QP5-3</b>	100	
	Black/4-Pole	<b>1492-QP5-4</b>	100	<b>1492-QP5-4</b>	100	
	Black/5-Pole	<b>1492-QP5-5</b>	50	<b>1492-QP5-5</b>	50	
	Black/6-Pole	<b>1492-QP5-6</b>	50	<b>1492-QP5-6</b>	50	
	Black/7-Pole	<b>1492-QP5-7</b>	50	<b>1492-QP5-7</b>	50	
	Black/8-Pole	<b>1492-QP5-8</b>	50	<b>1492-QP5-8</b>	50	
	Black/9-Pole	<b>1492-QP5-9</b>	50	<b>1492-QP5-9</b>	50	
	Black/10-Pole	<b>1492-QP5-10</b>	50	<b>1492-QP5-10</b>	50	
	Black/11-Pole	<b>1492-QP5-11</b>	50	<b>1492-QP5-11</b>	50	
	Black/12-Pole	<b>1492-QP5-12</b>	50	<b>1492-QP5-12</b>	50	
<b>Accessories</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>	
Mounting Rails						
1 m Symmetrical DIN (Steel)	<b>199-DR1</b>	10		<b>199-DR1</b>	10	
1 m Symmetrical DIN (Aluminum)	<b>1492-DR5</b>	10		<b>1492-DR5</b>	10	
1 m Hi-Rise Sym. DIN (Aluminum)	<b>1492-DR6</b>	2		<b>1492-DR6</b>	2	
1 m Angled Hi-Rise Sym. DIN (Steel)	<b>1492-DR7</b>	2		<b>1492-DR7</b>	2	
<b>End Barriers</b>	Grey	<b>1492-EBLC3</b>	20	1492-EBLDC3	20	
End Anchors and Retainers:						
Screwless End Retainer	<b>1492-ERL35</b>	20		<b>1492-ERL35</b>	20	
DIN Rail — Normal Duty	<b>1492-EAJ35</b>	100		<b>1492-EAJ35</b>	100	
DIN Rail — Heavy Duty	<b>1492-EAHJ35</b>	50		<b>1492-EAHJ35</b>	50	
Jumpers						
Plug-in Center Jumper — 50-Pole	<b>1492-CJLJ5-50</b>	10		<b>1492-CJLJ5-50</b>	10	
Plug-in Center Jumper — 10-Pole	<b>1492-CJLJ5-10</b>	20		<b>1492-CJLJ5-10</b>	20	
Plug-in Center Jumper — 9-Pole	1492-CJLJ5-9	20		1492-CJLJ5-9	20	
Plug-in Center Jumper — 8-Pole	<b>1492-CJLJ5-8</b>	20		<b>1492-CJLJ5-8</b>	20	
Plug-in Center Jumper — 7-Pole	<b>1492-CJLJ5-7</b>	20		<b>1492-CJLJ5-7</b>	20	
Plug-in Center Jumper — 6-Pole	<b>1492-CJLJ5-6</b>	20		<b>1492-CJLJ5-6</b>	20	
Plug-in Center Jumper — 5-Pole	<b>1492-CJLJ5-5</b>	20		<b>1492-CJLJ5-5</b>	20	
Plug-in Center Jumper — 4-Pole	<b>1492-CJLJ5-4</b>	60		<b>1492-CJLJ5-4</b>	60	
Plug-in Center Jumper — 3-Pole	<b>1492-CJLJ5-3</b>	60		<b>1492-CJLJ5-3</b>	60	
Plug-in Center Jumper — 2-Pole	<b>1492-CJLJ5-2</b>	60		<b>1492-CJLJ5-2</b>	60	
Other Accessories						
Group Marking Carrier	<b>1492-GM35</b>	25		<b>1492-GM35</b>	25	
Marking Systems						
Snap-In Marker Cards	<b>1492-M5X10</b> (144/card)	5		<b>1492-M5X10</b> (144/card)	5	
Snap-In Marker Cards	<b>1492-M5X5</b> (200/card)	5		<b>1492-M5X5</b> (200/card)	5	
Hinged Marker Card	<b>1492-MH5X10</b> (96/card)	5		—	—	