

Product Details and Certifications

Cross Reference RA Part Number: 1492-EBLD3 A

 **Product: 1492-EBLD3**

Description: 1492 Terminal Block, End Barrier, Gray (Standard), Qty. 25



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

| | |
|---------------------|---------------------------------|
| Bulletin Number | 1492 Terminal Block Accessories |
| Accessory Selection | Individual Accessory Selection |

SELECTION

1492 Accessory

Spring-Clamp Connection Terminal Blocks

Multi-Circuit Feed-Through Blocks

| | 1492-LD2 | | | 1492-LD3 | | | | 1492-L3QS | | | |
|--|--|-------------------|------------------------------|--|------------------------------|---------------------|--|--|------|---------------------|------------------------------------|
| Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block. | | | | | | | | | | | |
| Specifications | <i>Two-circuit feed-through terminal block</i> | | | <i>Two-circuit feed-through terminal block</i> | | | | <i>Side-by-side two circuit terminal block</i> | | | |
| Certifications | | | | | | | | | | | |
| Voltage Rating | 300V AC/DC | | 600V AC/DC | 600V AC/DC | | 800V AC/DC | 550V AC/DC | 600V AC/DC | | 800V AC/DC | 550V AC/DC |
| Maximum Current | 10 A | | 17.5 A | 20 A | 25 A | 24 A | 20 A | 25 A | 27 A | 24 A | 21 A |
| Wire Range (Rated Cross Section) | #28... 16 AWG | | 1.5 mm ² | #30... 12 AWG | | 2.5 mm ² | 0.5...2.5 mm ² (#20...14 AWG) | #26... 12 AWG | | 2.5 mm ² | 2.5 mm ² (20... 12 AWG) |
| Wire Strip Length | 0.39 in. (10 mm) | | | 0.39 in. (10 mm) | | | | 0.39 in. (10 mm) | | | |
| Density | 87 pcs/ft (285 pcs/m) | | | 59 pcs/ft (196 pcs/m) | | | | 59 pcs/ft (196 pcs/m) | | | |
| Housing Temperature Range | -58...+248 °F (-50...+120 °C) | | | -58...+248 °F (-50...+120 °C) | | | | -58...+248 °F (-50...+120 °C) | | | |
| Terminal Blocks | Cat. No. | Pkg Qty. | Cat. No. | Pkg Qty. | Cat. No. | Pkg Qty. | | | | | |
| Color | Grey | 1492-LD2 | 50 | 1492-LD3 | 25 | 1492-L3QS | 50 | | | | |
| | Red | 1492-LD2-RE | 50 | 1492-LD3-RE | 25 | 1492-L3QS-RE | 50 | | | | |
| | Blue | 1492-LD2-B | 50 | 1492-LD3-B | 25 | 1492-L3QS-B | 50 | | | | |
| | Black | 1492-LD2-BL | 50 | 1492-LD3-BL | 25 | 1492-L3QS-BL | 50 | | | | |
| | Green | 1492-LD2-G | 50 | 1492-LD3-G | 25 | 1492-L3QS-G | 50 | | | | |
| | Yellow | 1492-LD2-Y | 50 | 1492-LD3-Y | 25 | 1492-L3QS-Y | 50 | | | | |
| | Orange | 1492-LD2-OR | 50 | 1492-LD3-OR | 25 | 1492-L3QS-OR | 50 | | | | |
| | Brown | 1492-LD2-BR | 50 | 1492-LD3-BR | 25 | 1492-L3QS-BR | 50 | | | | |
| | White | 1492-LD2-W | 50 | 1492-LD3-W | 25 | 1492-L3QS-W | 50 | | | | |
| Accessories | Cat. No. | Pkg Qty. | Cat. No. | Pkg Qty. | Cat. No. | Pkg Qty. | | | | | |
| Mounting Rails | | | | | | | | | | | |
| 1 m Symmetrical DIN (Steel) | 199-DR1 | 10 | 199-DR1 | 10 | 199-DR1 | 10 | | | | | |
| 1 m Symmetrical DIN (Aluminum) | 1492-DR5 | 10 | 1492-DR5 | 10 | 1492-DR5 | 10 | | | | | |
| 1 m Hi-Rise Symmetrical DIN (Aluminum) | 1492-DR6 | 2 | 1492-DR6 | 2 | 1492-DR6 | 2 | | | | | |
| 1 m Angled Hi-Rise Sym. DIN (Steel) | 1492-DR7 | 2 | 1492-DR7 | 2 | 1492-DR7 | 2 | | | | | |
| End Barriers | Grey | 1492-EBLD2 | 50 | 1492-EBLD3 | 20 | 1492-EBL3Q | 50 | | | | |
| | Blue | 1492-EBLD2-B | 20 | 1492-EBLD3-B | 20 | 1492-EBL3Q-B | 50 | | | | |
| | Yellow | 1492-EBLD2-Y | 20 | 1492-EBLD3-Y | 20 | 1492-EBL3Q-Y | 50 | | | | |
| End Anchors and Retainers | | | | | | | | | | | |
| Screwless End Retainer | 1492-ERL35 | 20 | 1492-ERL35 | 20 | 1492-ERL35 | 20 | | | | | |
| DIN Rail — Normal Duty | 1492-EAJ35 | 100 | 1492-EAJ35 | 100 | 1492-EAJ35 | 100 | | | | | |
| DIN Rail — Heavy Duty | 1492-EAHJ35 | 50 | 1492-EAHJ35 | 50 | 1492-EAHJ35 | 50 | | | | | |
| Jumpers | | | | | | | | | | | |
| Plug-in Center Jumper — 50-Pole | — | — | 1492-CJK5-50 | 10 | — | — | | | | | |
| Plug-in Center Jumper — 10-Pole | 1492-CJL4-10 | 20 | 1492-CJK5-10 | 20 | — | — | | | | | |
| Plug-in Center Jumper — 9-Pole | — | — | 1492-CJK5-9 | 20 | — | — | | | | | |
| Plug-in Center Jumper — 8-Pole | — | — | 1492-CJK5-8 | 20 | — | — | | | | | |
| Plug-in Center Jumper — 7-Pole | — | — | 1492-CJK5-7 | 20 | — | — | | | | | |
| Plug-in Center Jumper — 6-Pole | — | — | 1492-CJK5-6 | 20 | — | — | | | | | |
| Plug-in Center Jumper — 5-Pole | 1492-CJL4-5 | 60 | 1492-CJK5-5 | 20 | — | — | | | | | |
| Plug-in Center Jumper — 4-Pole | 1492-CJL4-4 | 60 | 1492-CJK5-4 | 60 | — | — | | | | | |
| Plug-in Center Jumper — 3-Pole | 1492-CJL4-3 | 60 | 1492-CJK5-3 | 60 | — | — | | | | | |
| Plug-in Center Jumper — 2-Pole | 1492-CJL4-2 | 60 | 1492-CJK5-2 | 60 | — | — | | | | | |
| Other Accessories | | | | | | | | | | | |
| Reducing Sleeves #28...24 AWG (0.13...0.2 mm ²) | 1492-PSL2-2 | 100 | 1492-PSLS2-2 | 100 | 1492-PSL3-2 | 100 | | | | | |
| Reducing Sleeves #22...20 AWG (0.25...0.5 mm ²) | 1492-PSL2-5 | 100 | 1492-PSLS2-5 | 100 | 1492-PSL3-5 | 100 | | | | | |
| Reducing Sleeves #18 AWG (0.75...1.0 mm ²) | — | — | — | — | 1492-PSL3-10 | 100 | | | | | |
| Test Plug | 1492-TPL4 | 25 | — | — | 1492-TP23 | 20 | | | | | |
| | | | | | 1492-TPL5 | 25 | | | | | |
| Electrical Warning Plate | 1492-EWPL4 | 20 | — | — | 1492-EWPL5 | 20 | | | | | |
| Marking Systems | | | | | | | | | | | |
| Snap-In Marker Cards | 1492-M3X12 (120/card)* | 5 | 1492-M5X10 (144/card) | 5 | 1492-M5X10 (144/card) | 5 | | | | | |
| | 1492-M3X5 (100/card) | 5 | 1492-M5X5 (200/card) | 5 | 1492-M5X5 (200/card) | 5 | | | | | |
| Hinged Marker Cards | — | — | — | — | 1492-MH5X10 (96/card) | 5 | | | | | |

* May only be mounted in terminal block corner marking positions.

