

Product Details and Certifications

Cross Reference RA Part Number: 1492-EBLD4-Y A

 Product: **1492-EBLD4-Y**

Description: 1492 Terminal Block, End Barrier, Yellow, Qty. 20



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

SELECTION

1492 Accessory

Spring-Clamp Connection Terminal Blocks

Multi-Circuit Feed-Through Blocks

	1492-LD4			1492-LTF3		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.						
	Two-circuit feed-through terminal block			Three-circuit feed-through terminal block with multiple cross connection points		
Specifications						
Certifications		CSA	IEC		CSA	IEC
Voltage Rating	600V AC/DC		800V AC/DC	300V AC/DC		500V AC/DC
Maximum Current	25 A	30 A	32 A	15 A		20 A
Wire Range (Rated Cross Section)	#26...10 AWG		4 mm ²	#26...12 AWG		2.5 mm ²
Wire Strip Length	0.39 in. (10 mm)			0.39 in. (10 mm)		
Density	49 pcs/ft (163 pcs/m)			59 pcs/ft (196 pcs/m)		
Housing Temperature Range	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)		
Terminal Blocks		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.
Color	Grey	1492-LD4	20		1492-LTF3	25
	Red	1492-LD4-RE	20		—	—
	Blue	1492-LD4-B	20		—	—
	Black	1492-LD4-BL	20		—	—
	Green	1492-LD4-G	20		—	—
	Yellow	1492-LD4-Y	20		—	—
	Orange	1492-LD4-OR	20		—	—
	Brown	1492-LD4-BR	20		—	—
	White	1492-LD4-W	20		—	—
Accessories		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.
Mounting Rails						
1 m Symmetrical DIN (Steel)		199-DR1	10		199-DR1	10
1 m Symmetrical DIN (Aluminum)		1492-DR5	10		1492-DR5	10
1 m Hi-Rise Sym. DIN (Aluminum)		1492-DR6	2		1492-DR6	2
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7	2		1492-DR7	2
End Barriers	Grey	1492-EBLD4	20		1492-EBLTF3	20
	Blue	1492-EBLD4-B	20		—	—
	Yellow	1492-EBLD4-Y	20		—	—
End Anchors and Retainers						
Screwless End Retainer		1492-ERL35	20		1492-ERL35	20
DIN Rail — Normal Duty		1492-EAJ35	100		1492-EAJ35	100
DIN Rail — Heavy Duty		1492-EAHJ35	50		1492-EAHJ35	50
Jumpers						
Plug-in Center Jumper — 50-Pole		—	—		1492-CJK5-50	10
Plug-in Center Jumper — 10-Pole		1492-CJK6-10	20		1492-CJK5-10	20
Plug-in Center Jumper — 9-Pole		1492-CJK6-9	20		1492-CJK5-9	20
Plug-in Center Jumper — 8-Pole		1492-CJK6-8	20		1492-CJK5-8	20
Plug-in Center Jumper — 7-Pole		1492-CJK6-7	20		1492-CJK5-7	20
Plug-in Center Jumper — 6-Pole		1492-CJK6-6	20		1492-CJK5-6	20
Plug-in Center Jumper — 5-Pole		1492-CJK6-5	20		1492-CJK5-5	20
Plug-in Center Jumper — 4-Pole		1492-CJK6-4	60		1492-CJK5-4	60
Plug-in Center Jumper — 3-Pole		1492-CJK6-3	60		1492-CJK5-3	60
Plug-in Center Jumper — 2-Pole		1492-CJK6-2	60		1492-CJK5-2	60
Vertical Cross Connector*		—	—		1492-CJL5D	20
Other Accessories						
Reducing Sleeves 26...24 AWG (0.13...0.2 mm ²)		—	—		1492-PSLTF3-2	100
Reducing Sleeves 22...20 AWG (0.25...0.5 mm ²)		—	—		1492-PSLTF3-5	100
Test Plug		1492-TP23	20		—	—
Electrical Warning Plate		1492-EWPL6	20		—	—
Marking Systems						
Snap-In Marker Cards		1492-M6X10 (120/card)	5		1492-SM5X10 (144/card)	5
Snap-In Marker Cards		1492-M6X5 (200/card)	5		1492-M5X5 (200/card)	5

* Used to electrically connect 2 levels of 1492-LTF3