

Product Details and Certifications

Cross Reference RA Part Number: 1492-ED103 A

 Product: **1492-ED103**

Description: 1492 Panel Mount Block, , Pull apart, 3-Pole



Representative Photo Only (actual product may vary based on configuration sections)

PANEL MOUNT BLOCK DATA

Bulletin Number	1492 Panel Block
Base Block Type	Pull-Apart Blocks
Number of Poles	3 Pole
Terminal Type	Standard

CERTIFICATIONS AND APPROVALS

UR
CSA

For UL Certifications Directory:

<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

NEMA/EEMAC Terminal Blocks

Panel Mount Blocks



	1492-EC85	1492-ED103		
<p>Dimensions are not intended to be used for manufacturing purposes.</p>				
Specifications	5-pole terminal block. Pulls apart to disconnect all poles from the circuit.	3-pole terminal block. Pulls apart to disconnect all poles from the circuit.		
Certifications (See page 12-3)	UL/CSA	UL/CSA		
Voltage Rating	600V AC/DC	600V AC/DC		
Maximum Current (per pole)	25 A	60 A		
Wire Range (Rated Cross Section)*	#20...12 AWG (0.75...4 mm ²)	#14...4 AWG (2.5...25 mm ²)		
Wire Strip Length	0.38 in. (9.7 mm)	0.38 in. (9.7 mm)		
Recommended Tightening Torque	6...16 lb•in (0.7...1.8 N•m)	10...30 lb•in (1.1...3.4 N•m)		
Insulation Temperature Range	-40...+22 °F (-40...+105 °C)	-40...+221 °F (-40...+105 °C)		
Terminal Blocks	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Terminal Block	1492-EC85	1	1492-ED103	1
Accessories (page 12-109)	Cat. No.	Pkg Qty.	Cat. No.	Pkg Qty.
Jumpers: 2-Pole Uninsulated	1492-N38	50	1492-N38	50
Anchor Unit: (required every 12th block)	Not Required	—	Not Required	—
End Piece	Not Required	—	Not Required	—

* #8-32 screw.

* Both terminal blocks accept 1 wire per terminal.

