

# Product Details and Certifications

**Cross Reference RA Part Number: 1492-FPK224 A**

 **Product: 1492-FPK224**

Description: 1492 Terminal Block, Fuse Plug with Blown Fuse Indication (10 - 36 V), Black



Representative Photo Only (actual product may vary based on configuration sections)

## ***ACCESSORY SELECTION***

---

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

## ***SELECTION***

---

1492 Accessory

# Screw Connection Terminal Blocks

## Plug-In Style Terminal Blocks

	1492-J3P			1492-J3PTP			1492-JD3P		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.									
<b>Specifications</b>	Selectable component plug-in terminal block			Selectable component plug-in terminal block with test plug socket			Two Circuit selectable component plug-in terminal block		
<b>Certifications</b>		<b>CSA</b>	<b>IEC</b>		<b>CSA</b>	<b>IEC</b>		<b>CSA</b>	<b>IEC</b>
<b>Voltage Rating</b>	600V AC/DC	300V AC/DC	500V AC/DC	300V AC/DC		500V AC/DC	300V AC/DC		500V AC/DC
<b>Maximum Current</b>	20 A	10 A	24 A	20 A	10 A	24 A	20 A		24 A
<b>Wire Range (Rated Cross Section)</b>	#30...12 AWG		2.5 mm <sup>2</sup>	#30...12 AWG		2.5 mm <sup>2</sup>	#24...12 AWG	#30...12 AWG	2.5 mm <sup>2</sup>
<b>Wire Strip Length</b>	0.39 in. (10 mm)			0.39 in. (10 mm)			0.31 in. (8 mm)		
<b>Recommended Tightening Torque</b>	4.4 lb•in (0.5 N•m)			4.4 lb•in (0.5 N•m)			4.4 lb•in (0.5 N•m)		
<b>Density</b>	59 pcs/ft (196 pcs/m)			59 pcs/ft (196 pcs/m)			59 pcs/ft (196 pcs/m)		
<b>Housing Temperature Range</b>	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)		
<b>Short-Circuit Current Rating</b>	See page 12-42								
<b>Terminal Blocks</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>
<b>Color:</b>	Grey	1492-J3P	100	1492-J3PTP	100	1492-JD3P	50		
	Red	1492-J3P-RE	100	—	—	—	—		
<b>Accessories</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>
<b>Mounting Rails:</b>									
1 m Symmetrical DIN (Steel)		199-DR1	10	199-DR1	10	199-DR1	10		
1 m Symmetrical DIN (Aluminum)		1492-DR5	10	1492-DR5	10	1492-DR5	10		
1 m Hi-Rise Sym. DIN (Aluminum)		1492-DR6	2	1492-DR6	2	1492-DR6	2		
1 m Angled Hi-Rise Sym. DIN (Steel)		1492-DR7	2	1492-DR7	2	1492-DR7	2		
<b>End Barriers</b>		1492-EBJ3	50	1492-EBJ3	50	1492-EBJD3P	20		
<b>End Anchors and Retainers:</b>		1492-ERL35	20	1492-ERL35	20	1492-ERL35	20		
<b>Screwless End Retainer</b>									
DIN Rail — Normal Duty		1492-EAJ35	100	1492-EAJ35	100	1492-EAJ35	100		
DIN Rail — Heavy Duty		1492-EAHJ35	50	1492-EAHJ35	50	1492-EAHJ35	50		
<b>Jumpers* †:</b>		1492-CJLJ5-50	10	1492-CJLJ5-50	10	—	—		
Center Jumper — 50-Pole									
Center Jumper — 10-Pole		1492-CJLJ5-10	20	1492-CJLJ5-10	20	1492-CJJ5-10	20		
Center Jumper — 9-Pole		1492-CJLJ5-9	20	1492-CJLJ5-9	20	—	—		
Center Jumper — 8-Pole		1492-CJLJ5-8	20	1492-CJLJ5-8	20	—	—		
Center Jumper — 7-Pole		1492-CJLJ5-7	20	1492-CJLJ5-7	20	—	—		
Center Jumper — 6-Pole		1492-CJLJ5-6	20	1492-CJLJ5-6	20	—	—		
Center Jumper — 5-Pole		1492-CJLJ5-5	20	1492-CJLJ5-5	20	—	—		
Center Jumper — 4-Pole		1492-CJLJ5-4	60	1492-CJLJ5-4	60	1492-CJJ5-4	50		
Center Jumper — 3-Pole		1492-CJLJ5-3	60	1492-CJLJ5-3	60	1492-CJJ5-3	50		
Center Jumper — 2-Pole		1492-CJLJ5-2	60	1492-CJLJ5-2	60	1492-CJJ5-2	50		
Screw Type Jumper Notching Tool		—	—	—	—	1492-T1	1		
<b>Other Accessories:</b>		1492-EBJ16	20	1492-EBJ16	20	1492-PPJD3P	20		
Partition Plate									
Test Plug		—	—	1492-TP23	20	—	—		
Disconnect Plug		1492-DPL	50	1492-DPL	50	1492-DPL	50		
Component Plug		1492-CPL	50	1492-CPL	50	1492-CPL	50		
<b>Fuse Plug</b>		1492-FPK2	20	1492-FPK2	20	1492-FPK2	20		
Without Blown Fuse Indicator									
10...36V Blown Fuse Indicator		1492-FPK224	20	1492-FPK224	20	1492-FPK224	20		
35...70V Blown Fuse Indicator		1492-FPK248	20	1492-FPK248	20	1492-FPK248	20		
60...150V Blown Fuse Indicator		1492-FPK2120	20	1492-FPK2120	20	1492-FPK2120	20		
140...250V Blown Fuse Indicator		1492-FPK2250	20	1492-FPK2250	20	1492-FPK2250	20		
<b>Marking Systems:</b>		1492-M5X12 (144/card)	5	1492-M5X12 (144/card)	5	1492-SM5X10 (144/card)	5		
Snap-in marker cards									
Snap-in marker cards		1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5	1492-M5X5 (200/card)	5		

\* Cat. nos. 1492-J3P and J3PTP use screwless center jumpers. Cat. No. 1492-JD3P uses a screw-type center jumper.

† Use of Center Jumpers may affect spacings, requiring derating of terminal blocks. See the Terminal Block selection guide, pub. no. 1492-SG008\*.

