

# Product Details and Certifications

**Cross Reference RA Part Number: 1492-N23 D**



**Product: 1492-N23**

Description: 1492 Terminal Block Accessories, End Anchor, A-B  
Rail - Heavy Duty



Representative Photo Only (actual product may vary based on configuration sections)

## ***ACCESSORY SELECTION***

---

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

## ***SELECTION***

---

1492 Terminal Blocks and Wiring System

	1492-F8			1492-CA1		1492-CA1L	
Dimensions are not intended to be used for manufacturing purposes. <b>Note:</b> Height dimension is measured from top of rail to top of terminal block.							
	Terminal block, screw terminal with wire clamp.			Terminal block, tubular screw with pressure plate.		Terminal block, screw with large head, pressure plate.	
	<b>UL/CSA</b>			<b>UL/CSA</b>		<b>UL/CSA</b>	
	300V AC/DC			600V AC/DC		600V AC/DC	
Specifications							
Certifications							
Voltage Rating							
Maximum Current	25 A			55 A		55 A	
Wire Range (Rated Cross Section)	#22...#14 AWG (0.5...2.5 mm <sup>2</sup> )			#22...#8 AWG (0.5...10 mm <sup>2</sup> )		#22...#8 AWG (0.5...10 mm <sup>2</sup> )	
Wire Strip Length	0.25 in. (6.4 mm)			0.38 in. (9.7 mm)		0.38 in. (9.7 mm)	
Recommended Tightening Torque	6...14 lb•in (0.7...1.6 N•m)			8...16 lb•in (0.9...1.8 N•m)		8...16 lb•in (0.9...1.8 N•m)	
Density	30 pcs/ft (98 pcs/m)			30 pcs/ft (98 pcs/m)		30 pcs/ft (98 pcs/m)	
Insulation Temperature Range	-40...+221 °F (-40...+105 °C)			-40...+221 °F (-40...+105 °C)		-40...+221 °F (-40...+105 °C)	
<b>Terminal Blocks</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	
Color:	White	<b>1492-F8</b>	50	<b>1492-CA1</b>	50	<b>1492-CA1L</b>	50
	Two 3 ft Rails White	<b>1492-F8175</b> (88 pcs/rail)	1	<b>1492-CA1175</b> (88 pcs/rail)	1	<b>1492-CA1L175</b> (88 pcs/rail)	1
	Red	1492-F8RE	50	<b>1492-CA1RE</b>	50	<b>1492-CA1LRE</b>	50
	Blue	1492-F8B	50	<b>1492-CA1B</b>	50	1492-CA1LB	50
	Black	1492-F8BL	50	<b>1492-CA1BL</b>	50	1492-CA1LBL	50
	Green	1492-F8G	50	<b>1492-CA1G</b>	50	<b>1492-CA1LG</b>	50
	Yellow	1492-F8Y	50	<b>1492-CA1Y</b>	50	1492-CA1LY	50
	Brown	1492-F8BR	50	1492-CA1BR	50	1492-CA1LBR	50
	Violet	1492-F8VT	50	1492-CA1VT	50	1492-CA1LVT	50
	Grey	1492-F8GY	50	<b>1492-CA1GY</b>	50	1492-CA1LGY	50
	Orange	<b>1492-F1OR</b>	50	1492-CA1OR	50	<b>1492-CA1LOR</b>	50
<b>Accessories (page 12-109)</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	<b>Cat. No.</b>	<b>Pkg Qty.</b>	
Mounting Rails:							
A-B Rail	<b>1492-N1</b>	20	<b>1492-N1</b>	20	<b>1492-N1</b>	20	
3 ft Rigid A-B Rail	<b>1492-N22</b>	20	<b>1492-N22</b>	20	<b>1492-N22</b>	20	
3 ft High-Rise A-B Rail	<b>1492-N44</b>	2	<b>1492-N44</b>	2	<b>1492-N44</b>	2	
Standoff Brackets (use every 12 in.)	<b>1492-N25</b>	2	<b>1492-N25</b>	2	<b>1492-N25</b>	2	
End Barrier	<b>1492-N18</b>	50	<b>1492-N16</b>	50	<b>1492-N16</b>	50	
<b>End Anchors:</b> A-B Rail	<b>1492-N23</b>	10	<b>1492-N23</b>	10	<b>1492-N23</b>	10	
A-B Rail — Normal Duty	—	—	<b>1492-N47</b>	50	<b>1492-N47</b>	50	
A-B Rail — Retaining Clip — Light Duty	<b>1492-N2</b>	50	<b>1492-N2</b>	50	<b>1492-N2</b>	50	
Jumpers:							
2-pole Uninsulated	<b>1492-N14</b>	50	<b>1492-N3</b>	50	<b>1492-N3</b>	50	
50-pole Uninsulated	—	—	<b>1492-N30</b>	50	<b>1492-N30</b>	50	
Fanning Strip (12-pole can cut to desired length)	—	—	<b>1492-N20</b>	1	<b>1492-N20</b>	1	
Marking Systems	*	<b>1492-N5</b>	1	<b>1492-N45</b>	20	<b>1492-N45</b>	20

\* 1 sheet, 20 strips.