

Product Details and Certifications

Cross Reference RA Part Number: 1492-N42 A

 **Product: 1492-N42**

Description: 1492 Terminal Block Accessories, Uninsulated Side Jumper,
42 mm Center to Center, 2 Pole, White



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number	1492 Terminal Block Accessories
Accessory Selection	Individual Accessory Selection

SELECTION

1492 Terminal Blocks and Wiring System

Screw Connection Terminal Blocks

Mini Blocks

	1492-WM3				1492-WM4				1492-WMD1		
Dimensions are not intended to be used for manufacturing purposes. Note: Height dimension is measured from top of rail to top of terminal block.											
	1.14" (29 mm)				1.26" (32 mm)				1.76" (44.6 mm)		
Specifications	Single-circuit mini terminal block.				Single-circuit mini terminal block.				Two-circuit mini terminal block.		
Certifications											
Voltage Rating	300V AC/DC	500V AC/DC	300V AC/DC	420V AC/DC	300V AC/DC	500V AC/DC	300V AC/DC	420V AC/DC	300V AC/DC	300V AC/DC	500V AC/DC
Maximum Current	15 A	24 A	15 A	24 A	20 A	32 A	20 A	32 A	15 A	15 A	17.5 A
Wire Range (Rated Cross Section)	#30...14 AWG	0.5...2.5 mm ²	#22...14 AWG	2.5 mm ²	#22...12 AWG	0.5...4.0 mm ²	#22...12 AWG	4.0 mm ²	#22...16 AWG	0.5...1.5 mm ²	
Wire Strip Length	0.24 in. (6 mm)				0.39 in. (10 mm)				0.35 in. (9 mm)		
Recommended Tightening Torque	4.2...4.6 lb•in (0.47...0.52 N•m)				4.7...6.2 lb•in (0.53...0.70 N•m)				4.2...4.6 lb•in (0.47...0.52 N•m)		
Density	61 pcs/ft (200/m)				50 pcs/ft (166/m)				61 pcs/ft (200/m)		
Housing Temperature Range	-40...+195 °F (-40...+90 °C)				-40...+195 °F (-40...+90 °C)				-40...+195 °F (-40...+90 °C)		
Terminal Blocks		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Pkg Qty.
Color:	Grey	1492-WM3	50		1492-WM4	50		1492-WMD1	50		50
	Red	1492-WM3-RE	50		1492-WM4-RE	50		1492-WMD1-RE	50		50
	Blue	1492-WM3-B	50		1492-WM4-B	50		1492-WMD1-B	50		50
	Black	1492-WM3-BL	50		1492-WM4-BL	50		1492-WMD1-BL	50		50
	Green	1492-WM3-G	50		1492-WM4-G	50		1492-WMD1-G	50		50
	Yellow	1492-WM3-Y	50		1492-WM4-Y	50		1492-WMD1-Y	50		50
	Orange	1492-WM3-OR	50		1492-WM4-OR	50		1492-WMD1-OR	50		50
	Brown	1492-WM3-BR	50		1492-WM4-BR	50		1492-WMD1-BR	50		50
	White	1492-WM3-W	50		1492-WM4-W	50		1492-WMD1-W	50		50
Accessories		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Cat. No.	Pkg Qty.		Pkg Qty.
Mounting Rails:											
1 m Sym. mini DIN (Steel)		1492-DR3	5		1492-DR3	5		1492-DR3	5		5
End Barrier		1492-EBM3	50		1492-EBM4	50		1492-EBMD1	50		50
End Anchors and Retainers:											
Mini Screwless End Retainer		1492-ERL15	20		1492-ERL15	20		1492-ERL15	20		20
Mini DIN Anchor — Normal Duty		1492-EAJ15	50		1492-EAJ15	50		1492-EAJ15	50		50
Jumpers:											
Insulated Side Jumper		1492-SJM5-10 (10-pole)	10		1492-N42 (2-pole)	50		—	—		—
					1492-SJ6-10 (10-pole)	10		—	—		—
Side Jumper — 12-pole uninsulated		—	—		—	—		1492-SJMD5-12 (Uninsulated)	10		10
Center Jumper — 50-pole		—	—		1492-CJD6-50	5		—	—		—
Center Jumper — 10-pole		1492-CJM5-10	10		1492-CJD6-10	10		—	—		—
Center Jumper — 5-pole		—	—		1492-CJD6-5	10		—	—		—
Center Jumper — 4-pole		—	—		1492-CJD6-4	10		—	—		—
Center Jumper — 3-pole		1492-CJM5-3	10		1492-CJD6-3	10		—	—		—
Center Jumper — 2-pole		1492-CJM5-2	10		1492-CJD6-2	10		—	—		—
Center Jumper Link		1492-CJL5	10		1492-CJL6	10		—	—		—
Other Accessories:											
Partition Plate		1492-PPM3	50		1492-PPM3	50		1492-PPMD1	50		50
Test Plug		—	—		1492-TP28	10		—	—		—
Test Plug Adapter		1492-TA285	10		1492-TA40	10		—	—		—
Electrical Warning Plate (4-pole)		—	—		1492-EWP6-4	10		—	—		—
Marking Systems:											
Snap-in Marker Card		1492-MS5X5 (80/card)	5		1492-MS6X9 (80/card)	5		1492-MS5X5 (80/card)	5		5