

Product Details

Product: 150-A09NB-ND

Description: SMC-2, 9A, 400-480V AC 50/60Hz, 120V Interface Option



CONTROLLER DATA

Voltage	460V 60Hz
Current Rating	9A

SMC OPTIONS

Interface Option	Interface Option, 120V Control Voltage
------------------	--

Certifications and Approvals

CE	Marked (Open Type) Per Low Voltage Directive 73/23/EEC, 93/68/EEC
CSA	Certified (Open Type) (File No. LR 1234)
UL	Listed (Open Type) (File No. E96956)

Dimensions and Weight

Weight (kg / lbs)	2.25 / 4.95
-------------------	-------------

Recommended Spare Parts

NA	0	N/A
150-N4	1	N/A