

Product Details

Product: 150-A16NC-ND

Description: SMC-2, 16A, 500-575V AC 50/60Hz, 120V
Interface Option



CONTROLLER DATA

Voltage	575V 60Hz
Current Rating	16A

SMC OPTIONS

Interface Option	Interface Option, 120V Control Voltage
------------------	--

Certifications and Approvals

CE	Marked (Open Type) Per Low Voltage Directive 73/23/EEC, 93/68/EEC
CSA	Certified (Open Type) (File No. LR 1234)
UL	Listed (Open Type) (File No. E96956)

Dimensions and Weight

Weight (kg / lbs)	3.15 / 6.93
-------------------	-------------

Recommended Spare Parts

NA	0	N/A
150-N6	1	N/A