


Product Details

Product: 150-A240NCDA

Description: SMC Plus, 240A, 575V AC, Soft Stop Option



CONTROLLER DATA

Voltage	575V 60Hz
Current Rating	240A

OPTIONS

Control Options	Soft Stop
-----------------	-----------

Certifications and Approvals

CE	Marked (Open Type) Per Low Voltage Directive 73/23/EEC, 93/68/EEC
CSA	Certified (Open Type) (File No. LR 1234)
UL	Listed (Open Type) (File No. E96956)

Dimensions and Weight

Weight (kg / lbs)	30.0 / 66.0
-------------------	-------------