


Product Details

Product: 150-A24NCDB

Description: SMC Plus, 24A, 575V AC, Pump Control Option



CONTROLLER DATA

Voltage	575V 60Hz
Current Rating	24A

OPTIONS

Control Options	Pump Control
-----------------	--------------

Certifications and Approvals

CE	Marked (Open Type) Per Low Voltage Directive 73/23/EEC, 93/68/EEC
CSA	Certified (Open Type) (File No. LR 1234)
UL	Listed (Open Type) (File No. E96956)

Dimensions and Weight

Weight (kg / lbs)	4.50 / 9.90
-------------------	-------------

Recommended Spare Parts

40370-803-03	1	MODULE, 24AMP/600 VOLTS FOR MOTOR CONTROLLER
--------------	---	--