

Product Details and Certifications

Cross Reference RA Part Number: 150-C317NBD B

 **Product: 150-C317NBD**

Description: SMC-3, 3-Wire, Open Type, 317A, 480V 3-Phase
50/60 Hz Max, Control Voltage 100...240V AC



Representative Photo Only (actual product may vary based on configuration sections)

CONTROLLER DATA

Bulletin Number	150-C Solid State Controller
Enclosure Type	Open
Input Line Voltage	200..460V AC 50/60Hz
Control Voltage	100...240V AC
Phase	3 PH
Amperage Rating	317 A

CERTIFICATIONS AND APPROVALS

UL
CSA
EN/IEC
CE

For UL Certifications Directory:

<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

SMC-3 Controllers

The compact design of the SMC-3 controller provides three-phase control, increased intelligence, and unmatched performance in a cost-effective package with overload protection, integrated bypass, and motor system diagnostics. DIP switches and a rotary dial make secure setup easy. This controller features an electronic overload with adjustable trip class.

Modes of operation include the following:

- Soft Start
- Current Limit Start
- Selectable Kickstart
- Coast-to-rest
- Soft Stop

Catalog Number Explanation

Examples that are given in this section are not intended to be used for product selection. Use ProposalWorks to configure the SMC-Flex controller. ProposalWorks is available from <http://www.rockwellautomation.com/global/e-tools/overview.page>.

