

Product Details and Certifications

➔ Cross Reference RA Part Number: **PN-280570**

➔ Product: **150-S361NUD**

Description: 150 SMC-50 Controller Open, 361 A, , 100...240V AC (two 24V DC inputs and two relay outputs standard), 200...690V AC, 3-Phase, 50 and 60 Hz



Representative Photo Only (actual product may vary based on configuration sections)

CONTROLLER DATA

CONTROLLER RATINGS

361 A

ENCLOSURE TYPE

Open

INPUT LINE VOLTAGE

200...690V AC, 3-Phase, 50 and 60 Hz

CONTROL MODULE POWER VOLTAGE

100...240V AC (two 24V DC inputs and two relay outputs standard)

Catalog Number Explanation

150-S **361** **N** **U** **D**
a b c d e

a	
Bulletin Number	
Code	Description
150-S	SMC-50 Motor Controller

b			
Controller Type and Rating			
SMC-50 Controller with Internal Bypass		Solid-state SMC-50 Controller	
Code	Description	Code	Description
108	108 A with Internal Bypass	B1	90 A
135	135 A with Internal Bypass	B2	110 A
201	201 A with Internal Bypass	B3	140 A
251	251 A with Internal Bypass	B4	180 A
317	317 A with Internal Bypass	C1	210 A
361	361 A with Internal Bypass	C2	260 A
480	480 A with Internal Bypass	C3	320 A
		D1	361 A
		D2	420 A
		D3	520 A

c	
Enclosure Type	
Code	Description
N	Open

d	
Line Voltage	
Code	Description
B	200...480V AC, 3-Phase, 50 and 60 Hz
U	200...690V AC, 3-Phase, 50 and 60 Hz

e	
Control Voltage	
Code	Description
D	100...240V AC (two 24V DC inputs and two relay outputs standard)
R	24V DC (two 24V DC inputs and two relay outputs standard)