

Product Details and Certifications

➔ **Cross Reference RA Part Number: PN-280682**

➔ **Product: 150-S480NBD**

Description: 150 SMC-50 Controller Open, 480 A, , 100...240V AC (two 24V DC inputs and two relay outputs standard), 200...480V AC, 3-Phase, 50 and 60 Hz



Representative Photo Only (actual product may vary based on configuration sections)

CONTROLLER DATA

CONTROLLER RATINGS

480 A

ENCLOSURE TYPE

Open

INPUT LINE VOLTAGE

200...480V AC, 3-Phase, 50 and 60 Hz

CONTROL MODULE POWER VOLTAGE

100...240V AC (two 24V DC inputs and two relay outputs standard)

Catalog Number Explanation

Examples that are given in this section are not intended to be used for product selection. Use ProposalWorks to configure the SMC-50 controller. ProposalWorks is available from <http://www.rockwellautomation.com/global/e-tools/overview.page>.

150-S **480** **N** **B** **D**
 a b c d e

a	
Bulletin Number	
Code	Description
150-S	SMC-50 Motor Controller

b			
Controller Type and Rating			
SMC-50 Controller with Internal Bypass		Solid-state SMC-50 Controller	
Code	Description	Code	Description
108	108 A with Internal Bypass	B1	90 A
135	135 A with Internal Bypass	B2	110 A
201	201 A with Internal Bypass	B3	140 A
251	251 A with Internal Bypass	B4	180 A
317	317 A with Internal Bypass	C1	210 A
361	361 A with Internal Bypass	C2	260 A
480	480 A with Internal Bypass	C3	320 A
		D1	361 A
		D2	420 A
		D3	520 A

c	
Enclosure Type	
Code	Description
N	Open

d	
Line Voltage	
Code	Description
B	200 . . . 480V AC, 3-Phase, 50 and 60 Hz
U	200 . . . 690V AC, 3-Phase, 50 and 60 Hz

e	
Control Voltage	
Code	Description
D	100 . . . 240V AC (two 24V DC inputs and two relay outputs standard)
R	24V DC (two 24V DC inputs and two relay outputs standard)