

Product Details and Certifications

Cross Reference RA Part Number: PN-113491



Product: 1585J-E8HBJM-30

Description: 1585 EtherNet Cable, 8 Conductors, RJ45, Right Angle Male, Standard, RJ45, Straigh Male, Teal 600V, 100BASE-XT, 100 Mbit/s



Representative Photo Only (actual product may vary based on configuration sections)

FIRST CONNECTOR TYPE

Connector Type	RJ45
First Connector Orientation	Right Angle Male
Number of Conductors	8 Conductors

SECOND CONNECTOR TYPE

Second Connector Type	RJ45
Second Connector Orientation	Straigh Male

CABLE DATA

Cable Type	Teal 600V - Foil and Braided Shielding
Cable Bandwidth	100BASE-TX, 100 Mbit/s
Connector Feature	Standard
Crossover	No

CORD LENGTH DATA

Standard or Build-to-Order Cable Length	30 Meters
---	-----------

NOTES

First Connector Pinout:	Pinout:
Second Connector Pinout:	Pinout:
Cable Rating	600V