

# Product Details and Certifications

## Cross Reference RA Part Number: PN-113493

 **Product: 1585J-E8HBJM-40**

Description: 1585 EtherNet Cable, 8 Conductors, RJ45, Right Angle Male, Standard, RJ45, Straigh Male, Teal 600V, 100BASE-X, 100 Mbit/s



Representative Photo Only (actual product may vary based on configuration sections)

### ***FIRST CONNECTOR TYPE***

---

|                             |                  |
|-----------------------------|------------------|
| Connector Type              | RJ45             |
| First Connector Orientation | Right Angle Male |
| Number of Conductors        | 8 Conductors     |

### ***SECOND CONNECTOR TYPE***

---

|                              |              |
|------------------------------|--------------|
| Second Connector Type        | RJ45         |
| Second Connector Orientation | Straigh Male |

### ***CABLE DATA***

---

|                   |  |
|-------------------|--|
| Cable Type        | Teal 600V - Foil and Braided Shielding |
| Cable Bandwidth   | 100BASE-TX, 100 Mbit/s                 |
| Connector Feature | Standard                               |
| Crossover         | No                                     |

### ***CORD LENGTH DATA***

---

|   |           |
|---|-----------|
| Standard or Build-to-Order Cable Length | 40 Meters |
|---|-----------|

### ***NOTES***

---

|                          |         |
|--------------------------|---------|
| First Connector Pinout:  | Pinout: |
| Second Connector Pinout: | Pinout: |
| Cable Rating             | 600V    |