

# Product Details and Certifications

## Cross Reference RA Part Number: PN-113204



### Product: **1585J-L8HB-10**

Description: 1585 EtherNet Cable, 8 Conductors, RJ45, Left Angle Male, Standard, Flying Leads, Teal 600V, 100BASE-X, 100 Mbit/s



Representative Photo Only (actual product may vary based on configuration sections)

#### **FIRST CONNECTOR TYPE**

---

|                             |                 |
|-----------------------------|-----------------|
| Connector Type              | RJ45            |
| First Connector Orientation | Left Angle Male |
| Number of Conductors        | 8 Conductors    |

#### **SECOND CONNECTOR TYPE**

---

|                              |              |
|------------------------------|--------------|
| Second Connector Type        | Flying Leads |
| Second Connector Orientation | Flying Leads |

#### **CABLE DATA**

---

|                   |  |
|-------------------|--|
| Cable Type        | Teal 600V - Foil and Braided Shielding |
| Cable Bandwidth   | 100BASE-TX, 100 Mbit/s                 |
| Connector Feature | Standard                               |
| Crossover         | No                                     |

#### **CORD LENGTH DATA**

---

|   |           |
|---|-----------|
| Standard or Build-to-Order Cable Length | 10 Meters |
|---|-----------|

#### **NOTES**

---

|                          |                          |
|--------------------------|--------------------------|
| First Connector Pinout:  | Pinout:                  |
| Second Connector Pinout: | Flying Lead Color Codes: |
| Cable Rating             | 600V                     |