

Product Details and Certifications

Cross Reference RA Part Number: PN-112861



Product: 1585J-L8HBJM-0M4

Description: 1585 EtherNet Cable, 8 Conductors, RJ45, Left Angle Male, Standard, RJ45, Straight Male, Teal 600V, 100BASE-X, 100 Mbit/s, 600V



Representative Photo Only (actual product may vary based on configuration sections)

FIRST CONNECTOR TYPE

| | |
|-----------------------------|-----------------|
| Connector Type | RJ45 |
| First Connector Orientation | Left Angle Male |
| Number of Conductors | 8 Conductors |

SECOND CONNECTOR TYPE

| | |
|------------------------------|---------------|
| Second Connector Type | RJ45 |
| Second Connector Orientation | Straight Male |

CABLE DATA

| | |
|-------------------|--|
| Cable Type | Teal 600V - Foil and Braided Shielding |
| Cable Bandwidth | 100BASE-TX, 100 Mbit/s |
| Connector Feature | Standard |
| Crossover | No |

CORD LENGTH DATA

| | |
|---|------------|
| Standard or Build-to-Order Cable Length | 0.4 Meters |
|---|------------|

NOTES

| | |
|--------------------------|---------|
| First Connector Pinout: | Pinout: |
| Second Connector Pinout: | Pinout: |
| Cable Rating | 600V |