

# Product Details and Certifications

**Cross Reference RA Part Number: PN-113186**



**Product: 1585J-L8HBJM-35**

Description: 1585 EtherNet Cable, 8 Conductors, RJ45, Left Angle Male, Standard, RJ45, Straight Male, Teal 600V, 100BASE-X, 100 Mbit/s, 600V



Representative Photo Only (actual product may vary based on configuration sections)

## ***FIRST CONNECTOR TYPE***

---

|                             |                 |
|-----------------------------|-----------------|
| Connector Type              | RJ45            |
| First Connector Orientation | Left Angle Male |
| Number of Conductors        | 8 Conductors    |

## ***SECOND CONNECTOR TYPE***

---

|                              |               |
|------------------------------|---------------|
| Second Connector Type        | RJ45          |
| Second Connector Orientation | Straight Male |

## ***CABLE DATA***

---

|                   |  |
|-------------------|--|
| Cable Type        | Teal 600V - Foil and Braided Shielding |
| Cable Bandwidth   | 100BASE-TX, 100 Mbit/s                 |
| Connector Feature | Standard                               |
| Crossover         | No                                     |

## ***CORD LENGTH DATA***

---

|   |           |
|---|-----------|
| Standard or Build-to-Order Cable Length | 35 Meters |
|---|-----------|

## ***NOTES***

---

|                          |         |
|--------------------------|---------|
| First Connector Pinout:  | Pinout: |
| Second Connector Pinout: | Pinout: |
| Cable Rating             | 600V    |