

# Product Details and Certifications

## Cross Reference RA Part Number: PN-113170

 **Product: 1585J-L8HBJM-8**

Description: 1585 EtherNet Cable, 8 Conductors, RJ45, Left Angle Male, Standard, RJ45, Straight Male, Teal 600V, 100BASE-XT, 100 Mbit/s, 600V



Representative Photo Only (actual product may vary based on configuration sections)

### ***FIRST CONNECTOR TYPE***

---

Connector Type	RJ45
First Connector Orientation	Left Angle Male
Number of Conductors	8 Conductors

### ***SECOND CONNECTOR TYPE***

---

Second Connector Type	RJ45
Second Connector Orientation	Straight Male

### ***CABLE DATA***

---

Cable Type	Teal 600V - Foil and Braided Shielding
Cable Bandwidth	100BASE-TX, 100 Mbit/s
Connector Feature	Standard
Crossover	No

### ***CORD LENGTH DATA***

---

Standard or Build-to-Order Cable Length	8 Meters
---	----------

### ***NOTES***

---

First Connector Pinout:	Pinout:
Second Connector Pinout:	Pinout:
Cable Rating	600V