

Product Details and Certifications

Cross Reference RA Part Number: PN-22688



Product: 1585J-M4TBJM-1

Description: 1585 EtherNet Cable, 4 Conductors, RJ45, Straight Male, Standard, RJ45, Teal Robotic TPE, 100BASE-X, 100 Mbit/s



Representative Photo Only (actual product may vary based on configuration sections)

FIRST CONNECTOR TYPE

Connector Type	RJ45
First Connector Orientation	Straight Male
Number of Conductors	4 Conductors

SECOND CONNECTOR TYPE

Second Connector Type	RJ45
Second Connector Orientation	Straight Male

CABLE DATA

Cable Type	Teal Robotic TPE
Cable Bandwidth	100BASE-TX, 100 Mbit/s
Connector Feature	Standard
Crossover	No

CORD LENGTH DATA

Standard or Build-to-Order Cable Length	1 Meter
---	---------

NOTES

First Connector Pinout:	Pinout:
Second Connector Pinout:	Pinout:
Cable Rating	UL CMB, CMX, cUL, CMG, Standard TIA 568-B