

Product Details and Certifications

Cross Reference RA Part Number: PN-88275

 **Product: 1585J-M4UBJM-1**

Description: 1585 EtherNet Cable, 4 Conductors, RJ45, Straight Male, Standard, RJ45, Teal PUR, Shielded, 100BASE-Xt, 100 Mbit/s, High Flex Halogen Free, 10 million Cycles



Representative Photo Only (actual product may vary based on configuration sections)

FIRST CONNECTOR TYPE

Connector Type	RJ45
First Connector Orientation	Straight Male
Number of Conductors	4 Conductors

SECOND CONNECTOR TYPE

Second Connector Type	RJ45
Second Connector Orientation	Straight Male

CABLE DATA

Cable Type	Teal Halogen free PUR - Foil and Braided Shielding
Cable Bandwidth	100BASE-TX, 100 Mbit/s
Connector Feature	Standard
Crossover	No

CORD LENGTH DATA

Standard or Build-to-Order Cable Length	1 Meter
---	---------

NOTES

First Connector Pinout:	Pinout:
Second Connector Pinout:	Pinout:
Cable Rating	High Flex, PUR, Halogen Free, 10 Million Cycles