

Product Details and Certifications

Cross Reference RA Part Number: PN-112090



Product: 1585J-M8HBJM-0M8

Description: 1585 EtherNet Cable, 8 Conductors, RJ45, Straight Male, Standard, Teal 600V, 100BASE-TX, 100 Mbit/s, 600V, 0.8 Meter



Representative Photo Only (actual product may vary based on configuration sections)

FIRST CONNECTOR TYPE

First Connector Type	RJ45
First Connector Orientation	Straight Male
Number of Conductors	8 Conductors

SECOND CONNECTOR TYPE

Second Connector Type	RJ45
Second Connector Orientation	Straight Male

CABLE DATA

Cable Type	Teal 600V - Foil and Braided Shielding
Cable Bandwidth	100BASE-TX, 100 Mbit/s
Connector Feature	Standard
Crossover	No

CORD LENGTH DATA

Standard or Build-to-Order Cable Length	Build-to-Order Cable Length
Cable Length	0.8 M

NOTES

First Connector Pinout:	Pinout:
Second Connector Pinout:	Pinout:
Cable Rating	600V