

# Product Details and Certifications

## Cross Reference RA Part Number: PN-112840



### Product: **1585J-M8HBJM-2M5**

Description: 1585 EtherNet Cable, 8 Conductors, RJ45, Straight Male, Standard, Teal  
600V, 100BASE-Xt, 100 Mbit/s



Representative Photo Only (actual product may vary based on configuration sections)

#### **FIRST CONNECTOR TYPE**

---

Connector Type	RJ45
First Connector Orientation	Straight Male
Number of Conductors	8 Conductors

#### **SECOND CONNECTOR TYPE**

---

Second Connector Type	RJ45
Second Connector Orientation	Straight Male

#### **CABLE DATA**

---

Cable Type	Teal 600V - Foil and braided Shielding
Cable Bandwidth	100BASE-TX, 100 Mbit/s
Connector Feature	Standard
Crossover	No

#### **CORD LENGTH DATA**

---

Standard or Build-to-Order Cable Length	Build-to-Order Cable Length
Cable Length	2.5 Meters

#### **NOTES**

---

First Connector Pinout:	Pinout:
Second Connector Pinout:	Pinout:
Cable Rating	600V