

# Product Details and Certifications

**Cross Reference RA Part Number: PN-22787**

 **Product: 1585J-M8PBJM-20**

Description: 1585 EtherNet Cable, 8 Conductors, RJ45, Straight Male, Standard, Teal Riser PVC, 100BASE-Xt, 100 Mbit/s



Representative Photo Only (actual product may vary based on configuration sections)

## ***FIRST CONNECTOR TYPE***

---

Connector Type	RJ45
First Connector Orientation	Straight Male
Number of Conductors	8 Conductors

## ***SECOND CONNECTOR TYPE***

---

Second Connector Type	RJ45
Second Connector Orientation	Straight Male

## ***CABLE DATA***

---

Cable Type	Teal Riser PVC - Unshielded
Cable Bandwidth	100BASE-TX, 100 Mbit/s
Connector Feature	Standard
Crossover	No

## ***CORD LENGTH DATA***

---

Standard or Build-to-Order Cable Length	Build-to-Order Cable Length
Cable Length	20 Meters

## ***NOTES***

---

First Connector Pinout:	Pinout:
Second Connector Pinout:	Pinout:
Cable Rating	UL CMR, CMX; cUL CMG; Standard TIA 568-B