

Product Details and Certifications

Cross Reference RA Part Number: PN-34533



Product: **1585J-M8PBJM-60X**

Description: 1585 EtherNet Cable, 8 Conductors, RJ45, Straight Male, Standard, Teal Riser PVC, 100BASE-X, 100 Mbit/s, X-Over



Representative Photo Only (actual product may vary based on configuration sections)

FIRST CONNECTOR TYPE

Connector Type	RJ45
First Connector Orientation	Straight Male
Number of Conductors	8 Conductors

SECOND CONNECTOR TYPE

Second Connector Type	RJ45
Second Connector Orientation	Straight Male

CABLE DATA

Cable Type	Teal Riser PVC - Unshielded
Cable Bandwidth	100BASE-TX, 100 Mbit/s
Connector Feature	Standard
Crossover	Yes

CORD LENGTH DATA

Standard or Build-to-Order Cable Length	Build-to-Order Cable Length
Cable Length	60 Meters

NOTES

First Connector Pinout:	Pinout:
Second Connector Pinout:	Pinout:
Cable Rating	UL CMR, CMX; cUL CMG; Standard TIA 568-B