

Product Details and Certifications

Cross Reference RA Part Number: 1585J-M8TBJM-0M6 A



Product: 1585J-M8TBJM-0M6

Description: 1585 EtherNet Cable, 8 Conductors, RJ45, Straight Male, Standard, Teal Robotic TPE, 100BASE-X, 100 Mbit/s, Weld Splatter, Sun Light and Oil Resistant



Representative Photo Only (actual product may vary based on configuration sections)

FIRST CONNECTOR TYPE

Connector Type	RJ45
First Connector Orientation	Straight Male
Number of Conductors	8 Conductors

SECOND CONNECTOR TYPE

Second Connector Type	RJ45
Second Connector Orientation	Straight Male

CABLE DATA

Cable Type	Teal Robotic TPE
Cable Bandwidth	100BASE-TX, 100 Mbit/s
Connector Feature	Standard
Crossover	No

CORD LENGTH DATA

Standard or Build-to-Order Cable Length	Build-to-Order Cable Length
Cable Length	0.6 M

NOTES

First Connector Pinout:	Pinout:
Second Connector Pinout:	Pinout:
Cable Rating	Weld Splatter, sun light and oil resistant; UL CMG, CMX; cUL CMG; Standard TIA 568-B, flex rated