

# Product Details and Certifications

## Cross Reference RA Part Number: PN-21172

 **Product: 1585J-M8TBJM-3**

Description: 1585 EtherNet Cable, 8 Conductors, RJ45, Straight Male, Standard, Teal Robotic TPE, 100BASE-X, 100 Mbit/s, Weld Splatter, Sun Light and Oil Resistant



Representative Photo Only (actual product may vary based on configuration sections)

### ***FIRST CONNECTOR TYPE***

---

Connector Type	RJ45
First Connector Orientation	Straight Male
Number of Conductors	8 Conductors

### ***SECOND CONNECTOR TYPE***

---

Second Connector Type	RJ45
Second Connector Orientation	Straight Male

### ***CABLE DATA***

---

Cable Type	Teal Robotic TPE
Cable Bandwidth	100BASE-TX, 100 Mbit/s
Connector Feature	Standard
Crossover	No

### ***CORD LENGTH DATA***

---

Standard or Build-to-Order Cable Length	Build-to-Order Cable Length
Cable Length	3 Meters

### ***NOTES***

---

First Connector Pinout:	Pinout:
Second Connector Pinout:	Pinout:
Cable Rating	Weld Splatter, sun light and oil resistant; UL CMG, CMX; cUL CMG; Standard TIA 568-B, flex rated