

Product Details and Certifications

Cross Reference RA Part Number: 1606-XL480E-3W B



Product: **1606-XL480E-3W**

Description: Standard Power Supply, 24-28V DC, 480 W, 3 Phase,
480V AC wide range / 450-820V DC Input Voltage



Representative Photo Only (actual product may vary based on configuration sections)

POWER SUPPLY DATA

| | |
|----------------------|---|
| Bulletin Number | 1606 Switched Mode Power Supplies |
| Input Voltage | 400...500V AC wide ange / 450...820V DC |
| Output Voltage | 24-28V DC |
| Rated Output Watts | 480 W |
| Operational Range | 340...576V AC |
| Range Output Current | 20 A @ 24V, 18 A @ 28V |
| Power Boost | 25 A |
| No. of Phases | 3 Phase |

CERTIFICATIONS AND APPROVALS

UL
CE
IEC/EN
EMC

For UL Certifications Directory:

<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>