

Product Details and Certifications

Cross Reference RA Part Number: 1606-XLSBATASSY2 A



Product: **1606-XLSBATASSY2**

Description: Power Supply Accessories, 26Ah Battery Assembly w/ Mounting Bracket



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number	1606 Switched Mode Power Supplies
Accessory Selection	Individual Accessory Selection

SELECTION

1606 Accessories	26Ah Battery Assembly w/ Mounting Bracket
------------------	---

1606 Special Modules

Input Voltage	Output Power [W]	Output Voltage	Output Current [A]	Input Circuit Protection	Steady State Input Current 120/230 [V AC]	Parallel Operation	DC OK Relay	Cat. No.
18...36V DC	40	5.1	8	N/A	N/A	Yes	—	1606-XLDC40A
14...32.4V DC	92	24	3.8	N/A	N/A	—	—	1606-XLDC92D
100...240V AC, 110...300V DC	91	24	3.8	6 A SLOW BLOW FUSE OR 1489-A1C060/20 A*	1.02/0.48	Yes	✓	1606-XLSDNET4
100...240V AC, 110...300V DC	192	24	8	6 A SLOW BLOW FUSE OR 1489-A1C060/20 A*	2.13/1.00	Yes	✓	1606-XLSDNET8
100...120/200...240V AC	80	24...28	3.3	10 A SLOW BLOW FUSE OR 1489-A1C100/20 A*	1.50/0.68	No	—	1606-XLEDNET3
100...120/200...240V AC, 160...375V DC	60	24	2.5	10 A SLOW BLOW FUSE OR 1489-A1C100/16 A*	1.30/0.70	Yes‡	✓	1606-XL60DR
100...120/200...240V AC, 210...375V DC	120		5	10 A SLOW BLOW FUSE OR 1489-A1C100/16 A*	2.60/1.40	Yes‡	✓	1606-XL120DR
100...120/200...240V AC, 240...375V DC	240		10	10 A SLOW BLOW FUSE OR 1489-A1C100/10 A*	6.00/2.60	Yes‡	✓	1606-XL240DR
24V DC	720	V _{in} -5V typ	30	N/A	N/A*	—	—	1606-XLRED20-30
24V DC	960	V _{in} -6V typ	40	N/A	N/A§	—	—	1606-XLRED40
10...60V DC	384	V _{in} 1 -.9V typ	16➤	N/A	N/A	—	—	1606-XLPRED
10...60V DC	480	V _{in} 1 -.9V typ	20➤	N/A	N/A	—	—	1606-XLSRED
24...28	960	V _{in} 2.15 typ.	40	N/A	N/A	—	—	1606-XLSRED40
24...28	1920	V _{in} 2.7 typ.	80	N/A	N/A	—	—	1606-XLSRED80
24...60V DC	480	V _{in} 1 -.9V typ	20➤	N/A	N/A	—	✓	1606-XLERED

1606 Special Modules with UPS

Input Voltage	Output Power [W]	Output Voltage	Output Current [A]	Cat. No.
22.5...30V DC	240	22.5	10	⌘ 1606-XLS240-UPS
22.5...30V DC	240	22.5	10	1606-XLS240-UPSC
22.5...30V DC	240	12/22.5	5/10	1606-XLS240-UPSD
22.5...30V DC	240	22.5	10	1606-XLS240-UPSE
24...28.8V DC	480	22.5...27.8	20	1606-XLSBUFFER24
48...56V DC	960	45...54	10	1606-XLSBUFFER48

8

Bulletin 1606 Special Module Accessories

Description	Cat. No.
7 Ah/12V Battery Assembly with Bracket, for use with DC UPS	1606-XLSBATASSY1
7 Ah/12V Battery	1606-XLSBAT1
Battery bracket for 7 Ah/12V battery	1606-XLSBATBR1
26 Ah/12V Battery Assembly with Bracket, for use with DC UPS	1606-XLSBATASSY2
26 Ah/12V Battery	1606-XLSBAT2
Battery bracket for 26 Ah/12V battery	1606-XLSBATBR2

* To be used alongside 20, 30, and 40 A power supplies.

‡ Single/parallel operation (inclined characteristic) selectable (jumper).

§ To be used alongside 40 A power supplies (or smaller).

* Unit has internal (not accessible/replaceable) input fuse. Additional protection is not required if used on branch circuits ≤ UL test levels.

➤ See product specifications for proper use.

* **Cat. No. 1606-XLS240-UPS** is a charging module, used along side a power supply and a battery assembly. **The battery assembly must be ordered separately.** Order **Cat. No. 1606-XLSBATASSY1** for 7 Ah/ 12V battery assembly or **Cat. No. 1606-XLSBATASSY2** for 26 Ah/ 12V battery assembly. Consult local codes and regulations for installation.