

Product Details and Certifications

Cross Reference RA Part Number: 1609-500SBAT A

 **Product: 1609-500SBAT**

Description: 1609- Standard, 40°C Replacement Battery 500VA



Representative Photo Only (actual product may vary based on configuration sections)

ACCESSORY SELECTION

Bulletin Number	1609 Power Supplies
Accessory Selection	Individual Accessory Selection

SELECTION

1609 Accessories	(1) Standard 40°C Replacement Battery 500VA
------------------	---

Industrial Uninterruptible Power Supply

Catalog Number Explanation/ Product Selection/ Accessories

Catalog Number Explanation

1609 – U 500 N H C
a *b* *c* *d* *e*

a

Power Supply Type	
Code	Description
U	Uninterruptible Power Supply

c

Input/Output Voltage	
Code	Description
N	115V AC
E	208/230V AC

e

Network Management	
Code	Description
C	NMC included
	Can be left blank

b

Rated Output Power	
Code	Description
500	500VA (325 W)

d

Special Functions	
Code	Description
S	Standard Battery
H	High Temp. Battery
H	Can be left blank

Product Selection

Output Power	Input Voltage	Operating Temperature	Cat. No.	
			Without Network Management Card	With Network Management Card
500VA (325 W)	120V AC	0...40 °C	1609-U500NS	1609-U500NSC
		0...50 °C	1609-U500NH	1609-U500NHC
	208/230V AC	0...40 °C	1609-U500ES	1609-U500ESC
		0...50 °C	1609-U500EH	1609-U500EHC

Accessories

Description	Output Power	Cat. No.
40 °C replacement battery	500VA (325 W)	1609-500SBAT
50 °C replacement battery	500VA (325 W)	1609-500HBAT
Network management card		1609-NMC
Remote start cable		1609-RSC

