

# Product Details and Certifications

## Cross Reference RA Part Number: 1609-HDK1 A



Product: **1609-HDK1**

Description: 1609- Hardwire Kit (for 3 & 5 KVA UPS System)



Representative Photo Only (actual product may vary based on configuration sections)

### **ACCESSORY SELECTION**

---

|                     |                                |
|---------------------|--------------------------------|
| Bulletin Number     | 1609 Power Supplies            |
| Accessory Selection | Individual Accessory Selection |

### **SELECTION**

---

|                  |   |
|------------------|---|
| 1609 Accessories | (1) Hardwire Kit (for 3 & 5 KVA UPS System) |
|------------------|---|

# Industrial Uninterruptible Power Supply

Catalog Number Explanation/Product Selection/Accessories



## Bulletin 1609-P Series — Industrial Uninterruptible Power Supply

- Rugged industrial design
- Tower/rack compatible
- Extended runtime
- Battery management system
- Hot-swappable batteries
- Comprehensive network management
- Remote monitoring/configuration
- Double conversion online
- Pure sine wave output
- Frequency and voltage regulation
- Automatic internal bypass

### Certifications

UL Listed (File No. E190749, Guide YEDU)  
 CSA Certified (File LR1234)

### Standards Compliance

UL 1778  
 CE  
 CSA C22.2, No. 107  
 FCC

### Table of Contents

Overview ..... this page  
 Cat. No. Explanation this page  
 Product Selection ..... this page  
 Accessories..... this page  
 Specifications..... 8-33  
 Approx. Dimensions . 8-34

The Bulletin 1609-P has multiple options for remote management. Please see page 8-28 for details.

### Catalog Number Explanation

1609 –   P    3000    N    
                                   a                                  b                                  c

a

| Power Supply Type |   |
|-------------------|---|
| Code              | Description   |
| P                 | Double Conversion Online Uninterruptible Power Supply |

b

| Rated Output Power |                  |
|--------------------|------------------|
| Code               | Description      |
| 3000               | 3000VA (2100 W)  |
| 5000               | 5000VA (3500 W)  |
| 8000               | 8000VA (6400 W)  |
| 10000              | 10000VA (8000 W) |

c

| Input/Output Voltage |             |
|----------------------|-------------|
| Code                 | Description |
| N                    | 120V AC     |
| E                    | 208/230V AC |
| A                    | 230V AC     |

### Product Selection

| Output Power     | Input Voltage | Cat. No.           |
|------------------|---------------|--------------------|
| 3000VA (2100 W)  | 120V AC       | <b>1609-P3000N</b> |
| 3000VA (2100 W)  | 230V AC       | <b>1609-P3000A</b> |
| 5000VA (3500 W)  | 208/230V AC   | 1609-P5000E        |
| 8000VA (6400 W)  | 208/230V AC   | 1609-P8000E        |
| 10000VA (8000 W) | 208/230V AC   | 1609-P10000E       |

### Accessories

| Description  | Cat. No.         |
|--|------------------|
| Network management card (Standard on units 5 kVA and larger) | <b>1609-NMC</b>  |
| Remote start cable   | <b>1609-RSC</b>  |
| Replacement battery  | <b>1609-PBAT</b> |
| External battery pack  | 1609-PXBP        |
| 5000VA CCT (120V step down transformer)                      | 1609-5000CCT     |
| Rail kit   | 1609-PRK1        |
| <b>Hardwire kit (for 3 and 5 kVA units)</b>                  | <b>1609-HDK1</b> |
| Service bypass switch (16 kVA)                               | <b>1609-PSB1</b> |

