

# Product Details and Certifications

**Cross Reference RA Part Number: PN-25870**



**Product: 1756-DNB**

Description: DeviceNet Bridge / Scanner Module



Representative Photo Only (actual product may vary based on configuration sections)

## **STRATIX DATA**

---

Bulletin Number	1756 ControlLogix/GuardLogix System
DeviceNet Comm Rate	125 Kbps ( 500m Max), 250 Kbps (250m Max), 500 Kbps (100m Max)
Number of Nodes, Max	64
Current Draw @ 5.1V DC	400 mA
Current Draw @ 24V DC	0 mA
DeviceNet Current Draw @ 24V DC	60 mA
DeviceNet Voltage Range	11...25V DC CL 2/SELV
Power Dissipation	3.5 W
Thermal Dissipation	11.9 BTU/hr
Isolation Voltage	50V (continuous), Basic Insulation Type, Devicenet network to backpanel type tested at 853V AC for 60 s .No Insolation between USB and backplane
Slot Width	1
Module Location	Chassis-based, any slot
DeviceNet Port	1 DeviceNet open-style 5- or 10-pin linear plug
USB Port	USB 2.0, Full Speed (12 Mbps)
Wiring Category	1 - On DeviceNet ports 3- On USB ports
Enclosure Type Rating	None (open-style)