

Product Details and Certifications

Product: 2098-DSD-HV050X-DN

Description: HIGH VOLTAGE DRIVE, 11A/22A, ULTRA3000 W/DNET,INDE.

PRODUCT SELECTION

Drive Type	Ultra 3000 Digital Servo Drive
Input Power	High Voltage (230..480V ac)
Output Power	5 kW
Indexing	Indexing
Connections	DeviceNet Interface

Short Circuit Ratings Data Sheet for 2098-DSD-HV050X-DN

Continuous Current Output to DC Bus (A _{dc})	Peak Current Output	Inverter Continuous Current Output (A _{pk-avg})	Inverter Peak Current Output (A _{pk-pk})	SCCR w/o Fuse Protection		SCCR w/ Fuse Protection						Rating Reference	File Ref: UL	File Ref: CSA	Comments
				240V [kA]	480V [kA]	240V [kA]	Max Fuse Size [A]	Fuse Class	480V [kA]	Max Fuse Size [A]	Fuse Class				
--	--	11 A	22 A	--	5	--	--	--	200	--	CC, G, J, L, R, and T	NEC 1999 110-10	UL 508 C E14959	cUL	--