

Product: 20G1AND156AN0NNNNN
Description: PowerFlex 750-Series



Representative
Photo Only (actual product may vary based on
configuration selections)

BASE DRIVE INFORMATION

Bulletin Number	PowerFlex 755 AC Drive, with Embedded Ethernet/IP
Voltage Class	480 VAC, 3 PH
Current / Power Rating	156 Amps, 125HP ND, 100HP HD
Enclosure Type	Open Type
Input Type	AC Input with Precharge, no DC Terminals
Frame Size	Frame 6
Filtering & CM Cap Config	Filtered, CM Jumper Removed
Dynamic Braking	None