

## Hardware and Kits

### Section Hardware and Kits for Field Installation

Table 293 - Section Hardware and Kits

Description			Catalog Number	Price	Delivery Program	
Drip Hood <b>NOTE:</b> NEMA Types 1, 1 with gasket and 12 with drip hood fulfill NEMA Type 2 requirements	Drip hood for NEMA Type 1, 1 w/ gasket and 12. Drip hood is an overhang on top of a section. It provides protection from limited amounts of liquid or dirt dripping and/or running down the front of a section. Select one drip hood per section. Drip hoods fit 15" and 20" deep sections.	10" wide	2100H-DH10	\$145	SC	
		20" wide	2100H-DH20	290		
		25" wide	2100H-DH25	365		
		30" wide	2100H-DH30	435		
		35" wide	2100H-DH35	510		
		40" wide	2100H-DH40	580		
Pullbox	12" high x 20" wide	For 15" deep sections	NEMA Type 1 and Type 1 w/gasket	2100H-N2A1	540	
			NEMA Type 12	2100H-N2J1		
		For 20" deep sections	NEMA Type 1 and Type 1 w/gasket	2100H-N2A2		2100H-N2J2
			NEMA Type 12	2100H-N2J2		
	12" high x 25" wide	For 15" deep sections	NEMA Type 1 and Type 1 w/gasket	2100H-N2AA1	680	
			NEMA Type 12	2100H-N2AJ1		
For 20" deep sections		NEMA Type 1 and Type 1 w/gasket	2100H-N2AA2	2100H-N2AJ2		
		NEMA Type 12	2100H-N2AJ2			
Top Horizontal Wireway Pan	For locating units with handle interlocks in the topmost space factor of a vertical section	For use on Series A through E vertical sections	NEMA Type 1	2100H-NA4A1	90	
			NEMA Type 1 w/gasket and Type 12	2100H-NA4J1		
		For use on Series F through current series sections	NEMA Type 1	2100H-NA4A2	45	
			NEMA Type 1 w/gasket and Type 12	2100H-NA4J2		
Horizontal Wireway Cover	Covers either top or bottom wireway opening at front of vertical section	For 20" wide vertical section	2100H-NWW20	95		
		For 25" wide vertical section	2100H-NWW25	125		
		For 30" wide vertical section	2100H-NWW30	140		
		For 35" wide vertical section	2100H-NWW35	175		
		For 40" wide vertical section	2100H-NWW40	190		