

## Hardware and Kits

### Section Hardware and Kits for Field Installation

Table 293 - Section Hardware and Kits

| Description  |   |   | Catalog Number                   | Price       | Delivery Program |
|--|---|---|----------------------------------|-------------|------------------|
| Drip Hood<br><b>NOTE:</b> NEMA Types 1, 1 with gasket and 12 with drip hood fulfill NEMA Type 2 requirements | Drip hood for NEMA Type 1, 1 w/ gasket and 12. Drip hood is an overhang on top of a section. It provides protection from limited amounts of liquid or dirt dripping and/or running down the front of a section. Select one drip hood per section. Drip hoods fit 15" and 20" deep sections. | 10" wide  | 2100H-DH10                       | \$145       | SC               |
|  |   | 20" wide  | 2100H-DH20                       | 290         |                  |
|  |   | 25" wide  | 2100H-DH25                       | 365         |                  |
|  |   | 30" wide  | 2100H-DH30                       | 435         |                  |
|  |   | 35" wide  | 2100H-DH35                       | 510         |                  |
|  |   | 40" wide  | 2100H-DH40                       | 580         |                  |
| Pullbox  | 12" high x 20" wide   | For 15" deep sections                               | NEMA Type 1 and Type 1 w/gasket  | 2100H-N2A1  | 540              |
|  |   |   | NEMA Type 12                     | 2100H-N2J1  |                  |
|  |   | For 20" deep sections                               | NEMA Type 1 and Type 1 w/gasket  | 2100H-N2A2  |                  |
|  |   |   | NEMA Type 12                     | 2100H-N2J2  |                  |
|  | 12" high x 25" wide   | For 15" deep sections                               | NEMA Type 1 and Type 1 w/gasket  | 2100H-N2AA1 | 680              |
|  |   |   | NEMA Type 12                     | 2100H-N2AJ1 |                  |
| For 20" deep sections  |   | NEMA Type 1 and Type 1 w/gasket                     | 2100H-N2AA2                      |             |                  |
|  |   | NEMA Type 12  | 2100H-N2AJ2                      |             |                  |
| Top Horizontal Wireway Pan   | For locating units with handle interlocks in the topmost space factor of a vertical section   | For use on Series A through E vertical sections     | NEMA Type 1                      | 2100H-NA4A1 | 90               |
|  |   |   | NEMA Type 1 w/gasket and Type 12 | 2100H-NA4J1 |                  |
|  |   | For use on Series F through current series sections | NEMA Type 1                      | 2100H-NA4A2 | 45               |
|  |   |   | NEMA Type 1 w/gasket and Type 12 | 2100H-NA4J2 |                  |
| Horizontal Wireway Cover   | Covers either top or bottom wireway opening at front of vertical section  | For 20" wide vertical section                       | 2100H-NWW20                      | 95          |                  |
|  |   | For 25" wide vertical section                       | 2100H-NWW25                      | 125         |                  |
|  |   | For 30" wide vertical section                       | 2100H-NWW30                      | 140         |                  |
|  |   | For 35" wide vertical section                       | 2100H-NWW35                      | 175         |                  |
|  |   | For 40" wide vertical section                       | 2100H-NWW40                      | 190         |                  |